

Hammer drill bit suitable for SDS-Plus MX4



Execution:

- Four symmetrical 90° cutting edges ensure circular boreholes for optimal anchor mounting.
- Four-spiral flute geometry with large spiral for optimal removal of drilling dust.
- Centring point for easy, precise drilling.
- Welded, one-piece carbide element on dia. 5-10 mm bits. The resulting wider flute entrance leads to faster drilling progress.
- Enlarged chamfers for cutting reinforcing bars for a longer service life when hitting reinforcing bars
- New tapered spiral flute. A narrow spiral flute behind the drill tip ensures faster removal of drilling dust, increased drilling speed and reduced friction. Wide spiral flute towards the drive arbor for greater stability and reduced risk of breakage.
- Up to 20 % more boreholes per battery charge in concrete compared to standard drill bits with four cutting edges
- Made in Germany



Art. no.	70800 164
Brand	MILWAUKEE
Manufacturer Part Number	4932479369
Number of cutting edges	4 PCS
Tool holding device	Suitable for SDS-plus
Cutting edge diameter	10 mm
Chip flute length	50 mm
Length	115 mm
Cutting direction	Right-hand cutting
Gross Weight	2.714 kg
Product Group	7MC

EAN

4058546371630