



Finish : clear

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES 9239 468 44500 0833/000 p.190-1 Of 08/03/2011		HALOGEN LAMP INFRARED INDUSTRIAL 13169R CL 235V 500W					9239 468 44500 0833/000			25/02/2011					
REF. : PDM IRK 2010-053	DOCUMENTATION	UNIT mm	PROJ. EUROP 	2 SH	SH 190-1	10	SCA. 1	A4							
NAME : J.P. CHARLIER		VALIDATION : A. PICHARD		DR. FISCHER Europe											
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															

PRODUCT REQUIREMENT SHEET

See LV 75-032

MEASURING VOLTAGE	235V (stabilisation 3 min.)
MEASURING POSITION	Horizontal
LIFE TEST POSITION	Horizontal
BURNING POSITION	P15
SWITCHING CYCLE	Continuous
AGEING	1h at rated voltage

	VALUE UNIT	TOLERANCE
WATTAGE	500W	± 6 %
LIFE	5000 h	average
COLOR TEMPERATURE Clear lamp Lamp with reflector	NA NA	
FLUX	3000 lm	± 15%
WEIGHT	20 g	

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES :		HALOGEN LAMP						9239 468 44500			25/02/2011				
9239 468 44500		INFRARED INDUSTRIAL						0833/000							
0833/000 p. 190-2		13169R CL 235V 500W													
Of 08/03/2001		REF. : PDM IRK 2010-053		DOCUMENTATION	UNIT mm	PROJ EUROP	2 SH	SH	190-2	10			A4		
NOM : J.P. CHARLIER		VALIDATION : A. PICHARD						DR. FISCHER Europe							
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															