

## Product Datasheet

**Product code:** **E5341.CR.BG**

**Product type:** High Precision Cutters

**Made in:** Switzerland

**Description:** The 5341 is a high precision cutter belonging to the small tapered cutter family. This type of geometry and head dimensions offer an advantage to access small areas. The flush cutting edge is suitable to perform clean cuts with some tolerances. The 5341 is equipped with an ESD Ergo-tek handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.

**Head description:** Small Tapered

**Cutting edges:** Flush

**Cutting capacity:** soft wire 0.10-1.20 mm (38-17 AWG)

**Body material:** High carbon-chromium low alloy steel (100Cr6)

**Body finishing:** Sandblasted

**Handle material:** Ergo-tek - Thermoplastic Elastomer + PP compound

**Picture:**



**Dimensions:**

|         |                       |
|---------|-----------------------|
| OAL (A) | 125.0 mm – 4.921 inch |
| Width   | 60.0 mm – 2.362 inch  |
| Height  | 21.0 mm – 0.827 inch  |

**Head dimensions:**

|               |                      |
|---------------|----------------------|
| Width (C)     | 10.0 mm – 0.394 inch |
| Thickness (D) | 6.4 mm – 0.252 inch  |
| B             | 9.0 mm – 0.354 inch  |
| F             | 0.2 mm – 0.008 inch  |

