

SDUC boring bar, offset, steel, positive, right-hand

For longitudinal and copy turning with DC indexable insert

ATORN[®]

Application


For longitudinal and copy turning with DC indexable insert 55°.

Version

- Precision-made boring bar, **steel**, with internal cooling, offset, type D, attack angle 93.5°, tip angle 55°, clearance angle 7°

Advantage

- Narrow contour optimised for copying-turning work
- Positive body geometry ensures low cutting forces



Art. No.	17847 214
ISO name	A 1216 R/L SDUC R/L 07
Min. bore diameter	19.5 mm
Shaft diameter	16 mm
Clearance length	36 mm
Length	150 mm
Clamping surface height	15 mm
Programming size	11 mm
Suitable for indexable inserts	DC.. 0702..
Tool design	Right
DIN	8024

EAN-Code

4050293110395