VORTEX SHEDDING FLOWMETER AND TEMPERATURE TRANSMITTER

For Water and Coolant


FV101 Series





- ✓ ¼ FNPT to 4" Line Sizes
- ✓ LED Display
- ✓ 4 to 20 mA Output
- ✓ SSR Alarm
- ✓ Temperature Measurement Units Feature Separate 4 to 20 mA Output and SSR Alarm

The FV101 Series comprises in-line flowmeters that use the vortex shedding measuring principle. The fluid strikes a bluff body, imparting alternating vortices downstream of the bluff. This creates a pressure on a sensor body containing a piezoelectric crystal. The frequency of the sensor is proportional to the velocity of the fluid and is amplified and converted to a 4 to 20 mÅ output signal. Vortex technology yields a meter with no moving parts to hang up or wear. The meter has a bright 7.62 mm (0.3") high LED display of flow in èither liters or gallons. It can measure flow in any direction, and the display can be rotated 180° for viewing convenience. The FV101 Series can be used with non-viscous, clean, or dirty waterlike liquids that are compatible with brass, PVDF. and FKM. Measured fluids should not contain long fibers or a high level of abrasive solids. These meters are ideal for cooling loops using water or 50% glycols, and for water-soluble machine coolant (up to 10%). These applications are found in most process industries, including rubber, steel, fabrication, manufacturing, refining, paper, chemical, food, petrochemical, and power. Do not use on flammable liquids or on gases such as air.



SPECIFICATIONS

Accuracy: ±2% FS Repeatability: ±0.25% FS Alarm Deadband: 5% FS Response Time: User selectable

from 0.9 to 7.5 seconds

Max Flow: Over range occasionally

up to 125% of capacity

Temperature

Accuracy: ±1% FS

Response Time: 1.8 s to 63% of flow

Alarm Deadband: 2%

Display: 3-digit, 7.62 mm (0.3") high numeric LED that flashes below setpoint


Maximum Operating Pressure: 2" and Smaller: 20 bar (300 psig) 3 and 4": 13 bar (200 psig) **Operating Temperature:**

2 to 99°C (35 to 210°F) **Enclosure Rating:**


IP65: Type 1, 3, 4, 12, and 13 Analog Output: 4 to 20 mA

(600 Ω @ 24 Vdc)


FV100 Pressure Drop Chart




Installation: 10 pipe diameters upstream and 5 downstream recommended





Wiring for FV100-T Series






Wiring for FV100 Series





Ø = diameter

Dimensions (¼ thru 2" sizes)



Size	mm (inch)							
(inch)	Α	В	C	D	Е	F		
1/4, 1/2	82	41	80	23	69	29		
	(3.25)	(1.62)	(3.13)	(0.91)	(2.74)	(1.15)		
³ ⁄ ₄ , 1	115	58	103	53	106	45		
	(4.54)	(2.27)	(4.04)	(2.08)	(4.19)	(1.78)		
1½, 2	173	87	120	71	106	45		
	(6.82)	(3.41)	(4.71)	(2.80)	(4.19)	(1.78)		

To Order							
Flowmeter Model	Flowmeter/ Temperature Transmitter		Flow Range (GPM)		Pressure Drop psid	Weight	
No.	Model No.	Connection	Min	Max	Max	kg (lb)	
FV101		1/4 FNPT	0.4	4	9.2	1.3 (2.8)	
FV102	1	½ FNPT	1.2	12	3.6	1.2 (2.6)	
FV103	FV103-T	¾ FNPT	2.5	25	3.6	2.9 (6.3)	
FV104	FV104-T	1 FNPT	5	50	9.5	2.7 (5.9)	
FV105	FV105-T	1½ FNPT	10	100	4.8	5.9 (13)	
FV106	FV106-T	2 FNPT	20	200	4.9	4.8 (10.5)	
FV107	FV107-T	3" ANSI RF	30	300	1.3	19 (42)	
FV108	FV108-T	4" ANSI RF	60	600	1.3	25 (55)	

Accessories

Model No.	Description	
FV100-C1	Replacement 1 m (3') cable for FV100 Series	
FV100-C3	3 m (9.8') cable for FV100 Series	
FV100-C10	10 m (32.8') cable for FV100 Series	
FV100-CT2	Replacement 2 m (6.5') cable FV100-T Series	
FV100-CT5	5 m (16.4') cable for FV100-T Series	
FV100-CT10	10 m (32.8') cable for FV100-T Series	
PSR-24L	24 Vdc regulated power supply	

Comes complete with operator's manual and 1 m (3') cable.

Ordering Examples: FV101, 1/4 FNPT vortex meter, 0.4 to 4 GPM.

FV104, 1 FNPT 5 to 50 GPM meter.