



**SAFETY DATA SHEET**  
DOFF FERTILISER

Page: 1

Compilation date: 03/05/2017

Revision No: 1

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** DOFF FERTILISER

**Product code:** F-M

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** PC12: Fertilizers.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** Doff Portland Limited

Aerial Way

Hucknall

Nottingham

NG15 6DW

UK

**Tel:** +(44) 115 9834 300

**Email:** [help@doff.co.uk](mailto:help@doff.co.uk)

**1.4. Emergency telephone number**

**Emergency tel:** +(44) 115 9834 300

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** This product has no classification under CLP.

**2.2. Label elements**

**Label elements:**

**Precautionary statements:** P102: Keep out of reach of children.

P103: Read label before use.

P264: Wash hands thoroughly after handling.

P501: Dispose of contents/container to Local authority regulations.

**2.3. Other hazards**

**PBT:** This product is not identified as a PBT/vPvB substance.

**Section 3: Composition/information on ingredients**

**3.2. Mixtures**

**Contains:** This product does not contain any substances, nor concentration levels thereof, that require marking or that need to be declared.

[cont...]

# SAFETY DATA SHEET

DOFF FERTILISER

Page: 2

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. If irritation persists seek medical attention.

**Ingestion:** Wash out mouth with water. Do not induce vomiting.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** No data available.

**Inhalation:** There may be irritation of the nose and upper respiratory tract.

### 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** May form flammable / explosive dust-air mixture. In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Do not create dust.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Transfer to a closable, labelled salvage container for disposal by an appropriate method. Wash the spillage site with large amounts of water.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

[cont...]

# SAFETY DATA SHEET

DOFF FERTILISER

Page: 3

## 7.1. Precautions for safe handling

**Handling requirements:** Ensure there is sufficient ventilation of the area. Avoid the formation or spread of dust in the air. For outdoor use only.

## 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. KEEP OUT OF THE REACH OF CHILDREN.

**Suitable packaging:** Must only be kept in original packaging.

## 7.3. Specific end use(s)

**Specific end use(s):** PC12: Fertilizers.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Workplace exposure limits:** No data available.

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area. For outdoor use only.

**Respiratory protection:** Respiratory protection not required under normal use conditions. If dust concentration is high wear a suitable dust mask (EN143, EN149, FP1).

**Hand protection:** No special requirements under normal conditions of use.

**Eye protection:** No special requirements under normal conditions of use.

**Skin protection:** No special requirements under normal conditions of use.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Powder

**Colour:** Brown

**Odour:** Characteristic odour

**Solubility in water:** Miscible

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

[cont...]

# SAFETY DATA SHEET

DOFF FERTILISER

Page: 4

## 10.3. Possibility of hazardous reactions

**Hazardous reactions:** No data available.

## 10.4. Conditions to avoid

**Conditions to avoid:** Heat. Flames.

## 10.5. Incompatible materials

**Materials to avoid:** No data available.

## 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes. Ammonia

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Toxicity values:** No data available.

### Symptoms / routes of exposure

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** No data available.

**Inhalation:** There may be irritation of the nose and upper respiratory tract.

## Section 12: Ecological information

### 12.1. Toxicity

**Ecotoxicity values:** No data available.

### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No data available.

### 12.4. Mobility in soil

**Mobility:** No data available.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

**Other adverse effects:** No data available.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Disposal should be in accordance with Local Authority Regulations.

[cont...]

# SAFETY DATA SHEET

DOFF FERTILISER

Page: 5

**Disposal of packaging:** Disposal should be in accordance with Local Authority Regulations.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Fertiliser (Mammalian, Meat and Bone Meal) Regulations 1996.

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.

[final page]