


HP 5400R zL2 Switch Series



Key features

- Redundant Management
- Advanced access layer, distribution, and core
- Integrated L2 to L4 intelligent edge feature set
- Enterprise-class resiliency with hitless failover and power supply redundancy
- HP AllianceOne integrated
- Scalable 10/100/1000 and 10GbE connectivity with full PoE+ provisioning

Product overview

The HP 5400R zL2 Switch Series consists of advanced intelligent switches in the HP modular chassis product line, which includes 6-slot and 12-slot chassis and associated modules and bundles. The foundation for the switch series is a purpose-built, programmable ProVision ASIC that allows the most demanding networking features, such as Quality of Service (QoS) and security, to be implemented in a scalable yet granular fashion. With 10/100, Gigabit Ethernet, and 10 Gigabit Ethernet interfaces, redundant management availability, full PoE+ capability on all ports simultaneously with internal power supplies, integrated Layer 3 features, and HP AllianceOne solutions, the 5400R zL2 switch series offers excellent investment protection, flexibility, and scalability, as well as ease of deployment, operation, and maintenance.

Features and benefits

Software-defined networking

- OpenFlow

supports OpenFlow 1.0 and 1.3 specifications to enable SDN by allowing separation of the data (packet forwarding) and control (routing decision) paths

Quality of Service (QoS)

- Advanced classifier-based QoS

classifies traffic using multiple match criteria based on Layer 2, 3, and 4 information; applies QoS policies such as setting priority level and rate limit to selected traffic on a per-port or per-VLAN basis

- Layer 4 prioritization
 - enables prioritization based on TCP/UDP port numbers
- Traffic prioritization
 - allows real-time traffic classification into eight priority levels mapped to eight queues
- Bandwidth shaping
 - Port-based rate limiting
 - provides per-port ingress-/egress-enforced increased bandwidth
 - Classifier-based rate limiting
 - uses an access control list (ACL) to enforce increased bandwidth for ingress traffic on each port
 - Reduced bandwidth
 - provides per-port, per-queue egress-based reduced bandwidth
- Class of Service (CoS)
 - sets the IEEE 802.1p priority tag based on IP address, IP Type of Service (ToS), Layer 3 protocol, TCP/UDP port number, source port, and DiffServ

Management

- Remote intelligent mirroring
 - mirrors selected ingress/egress traffic based on ACL, port, MAC address, or VLAN to a local or remote HP 8200 zL, 6600, 6200 yL, 5400 zL, 5400R, 3500, or 3800 Switch located anywhere on the network
- RMON, XRMON, and sFlow v5
 - provide advanced monitoring and reporting capabilities for statistics, history, alarms, and events
- IEEE 802.1AB Link Layer Discovery Protocol (LLDP)
 - advertises and receives management information from adjacent devices on a network, facilitating easy mapping by network management applications
- Uni-Directional Link Detection (UDLD)
 - monitors a cable between two switches and shuts down the ports on both ends if the cable is broken, turning the bidirectional link into a unidirectional one; this prevents network problems such as loops
- Management simplicity
 - provides common software features and CLI implementation across all HP ProVision-based switches (including the zL and yL switches)
- Command authorization
 - leverages RADIUS to link a custom list of CLI commands to an individual network administrator's login; an audit trail documents activity
- Friendly port names
 - allows assignment of descriptive names to ports
- Dual flash images
 - provides independent primary and secondary operating system files for backup while upgrading
- Multiple configuration files
 - stores easily to the flash image
- Comware CLI
 - Comware-compatible CLI
 - bridges the experience of HP Comware CLI users who are using the HP ProVision software CLI

- Display and fundamental Comware CLI commands
 - are embedded in the switch CLI as native commands; display output is formatted as on Comware-based switches, and fundamental commands provide a Comware-familiar initial switch setup
- Configuration Comware CLI commands
 - when Comware commands are entered, CLI help is elicited to formulate the correct ProVision software CLI command

Connectivity

- IEEE 802.3az Energy Efficient Ethernet
 - lowers power consumption in periods of low link usage (supported on v2 zL 10/100/1000 and 10/100 modules)
- IEEE 802.3af Power over Ethernet (PoE)
 - provides up to 15.4 W per port to IEEE 802.3af-compliant PoE-powered devices such as IP phones, wireless access points, and security cameras
- IEEE 802.3at Power over Ethernet Plus
 - provides up to 30 W per port, for up to 288 ports simultaneously, for PoE- and PoE+-powered devices, such as video IP phones, IEEE 802.11n wireless access points, and advanced pan/zoom/tilt security cameras
- Prestandard PoE support
 - detects and provides power to prestandard PoE devices
- High-density port connectivity
 - provides up to 12 interface module slots and up to 288 wire-speed 10/100/1000 PoE-enabled ports or 96 10-GbE ports per system
- Jumbo frames
 - on Gigabit Ethernet and 10-Gigabit Ethernet ports, jumbo frames allow high-performance remote backup and disaster-recovery services
- Auto-MDIX
 - provides automatic adjustments for straight-through or crossover cables on all 10/100 and 10/100/1000 ports
- IPv6
 - IPv6 host
 - enables switches to be managed in an IPv6 network
 - Dual stack (IPv4 and IPv6)
 - transitions from IPv4 to IPv6, supporting connectivity for both protocols
 - MLD snooping
 - forwards IPv6 multicast traffic to the appropriate interface
 - IPv6 ACL/QoS
 - supports ACL and QoS for IPv6 network traffic
 - IPv6 routing
 - supports static and OSPFv3 routing protocols
 - 6in4 tunneling
 - supports encapsulation of IPv6 traffic in IPv4 packets

Performance

- High-speed, high-capacity architecture
 - 2 Tbps crossbar switching fabric provides intra-module and inter-module switching with 785.7 million pps throughput on the purpose-built ProVision ASICs
- Selectable queue configurations
 - allows for increased performance by selecting the number of queues and associated memory buffering that best meet the requirements of the network applications

Resiliency and high availability

- Virtual Router Redundancy Protocol (VRRP)
 - allows groups of two routers to dynamically back each other up to create highly available routed environments for IPv4 and IPv6 networks
- Nonstop switching
 - improves network availability to better support critical applications such as unified communication and mobility; interface and fabric modules continue switching traffic during failover from active to standby management module
- Nonstop routing
 - enhances Layer 3 high availability; OSPFv2/v3 and VRRP will continue to operate and route network traffic during failover from an active to a standby management module
- Redundant management and power
 - provide enhanced system availability and continuity of operations
- IEEE 802.1s Multiple Spanning Tree Protocol
 - provides high link availability in multiple VLAN environments by allowing multiple spanning trees; encompasses IEEE 802.1D Spanning Tree Protocol and IEEE 802.1w Rapid Spanning Tree Protocol
- IEEE 802.3ad Link Aggregation Control Protocol (LACP) and HP port trunking
 - support up to 144 trunks, each with up to eight links (ports) per trunk
- Distributed trunking
 - enables loop-free and redundant network topology without using Spanning Tree Protocol; allows a server or switch to connect to two switches using one logical trunk for redundancy and load sharing
- Optional redundant power supply
 - provides uninterrupted power and allows hot-swapping of the redundant power supplies when installed
- Hot-swappable modules
 - allows dissimilar modules, and power supplies in a redundant power supply configuration to be added or swapped without interrupting the network
- Sparing simplicity
 - HP zL-common accessories (interface modules and power supplies)
- Uplink Failure Detection
 - provides active-standby network path redundancy for servers that are configured for active-standby NIC teaming
- SmartLink
 - provides easy-to-configure link redundancy of active and standby links

Layer 2 switching

- VLAN support and tagging
 - supports the IEEE 802.1Q standard and 2,048 VLANs simultaneously
- IEEE 802.1v protocol VLANs
 - isolate select non-IPv4 protocols automatically into their own VLANs

- GARP VLAN Registration Protocol
allows automatic learning and dynamic assignment of VLANs
- IEEE 802.1ad Q-in-Q
increases the scalability of an Ethernet network by providing a hierarchical structure; connects multiple LANs on a high-speed campus or metro network
- MAC-based VLAN
provides granular control and security; uses RADIUS to map a MAC address/user to specific VLANs (requires v2 modules)
- Rapid Per-VLAN Spanning Tree (RPVST+)
allows each VLAN to build a separate spanning tree to improve link bandwidth usage; is compatible with PVST+
- HP switch meshing
dynamically load balances across multiple active redundant links to increase available aggregate bandwidth; allows concurrent Layer 3 routing with v2 modules

Layer 3 services

- User Datagram Protocol (UDP) helper function
allows UDP broadcasts to be directed across router interfaces to specific IP unicast or subnet broadcast addresses and prevents server spoofing for UDP services such as DHCP
- Loopback interface address
defines an address in Routing Information Protocol (RIP) and Open Standard Path First (OSPF), improving diagnostic capability
- Route maps
provide more control during route redistribution; allow filtering and altering of route metrics

Layer 3 routing

- Static IP routing
provides manually configured routing for both IPv4 and IPv6 networks
- Routing Information Protocol (RIP)
provides RIPv1 and RIPv2 routing
- OSPF
provides OSPFv2 for IPv4 routing and OSPFv3 for IPv6 routing
- Policy-based routing
uses a classifier to select traffic that can be forwarded based on policy set by the network administrator (requires v2 modules)
- Border Gateway Protocol (BGP)
provides IPv4 Border Gateway Protocol routing, which is scalable, robust, and flexible

Security

- Access control lists (ACLs)
provide filtering based on the IP field, source/destination IP address/subnet, and source/destination TCP/UDP port number on a per-VLAN or per-port basis
- Multiple user authentication methods
 - IEEE 802.1X users per port
provides authentication of multiple IEEE 802.1X users per port
 - Web-based authentication
authenticates from a Web browser for clients that do not support IEEE 802.1X supplicant

- MAC-based authentication
 - client is authenticated with the RADIUS server based on the client's MAC address
- Concurrent IEEE 802.1X, Web, and MAC authentication schemes per port
 - switch port accepts up to 32 sessions of IEEE 802.1X, Web, and MAC authentications
- Virus throttling
 - detects traffic patterns typical of worm-type viruses and either throttles or entirely prevents the virus from spreading across the routed VLANs or bridged interfaces without requiring external appliances
- DHCP protection
 - blocks DHCP packets from unauthorized DHCP servers, preventing denial-of-service attacks
- Secure management access
 - delivers secure encryption of all access methods (CLI, GUI, or MIB) through SSHv2, SSL, and/or SNMPv3
- Switch CPU protection
 - provides automatic protection against malicious network traffic trying to shut down the switch
- ICMP throttling
 - defeats ICMP denial-of-service attacks by enabling any switch port to automatically throttle ICMP traffic
- Identity-driven ACL
 - enables implementation of a highly granular and flexible access security policy and VLAN assignment specific to each authenticated network user
- STP BPDU port protection
 - blocks Bridge Protocol Data Units (BPDUs) on ports that do not require BPDUs, preventing forged BPDU attacks
- Dynamic IP lockdown
 - works with DHCP protection to block traffic from unauthorized hosts, preventing IP source address spoofing
- Dynamic ARP protection
 - blocks ARP broadcasts from unauthorized hosts, preventing eavesdropping or theft of network data
- STP root guard
 - protects the root bridge from malicious attacks or configuration mistakes
- Detection of malicious attacks
 - monitors 10 types of network traffic and sends a warning when an anomaly that potentially can be caused by malicious attacks is detected
- Port security
 - allows access only to specified MAC addresses, which can be learned or specified by the administrator
- MAC address lockout
 - prevents particular configured MAC addresses from connecting to the network
- Source-port filtering
 - allows only specified ports to communicate with each other
- RADIUS/TACACS+
 - eases switch management security administration by using a password authentication server
- Secure shell
 - encrypts all transmitted data for secure remote CLI access over IP networks

- Secure Sockets Layer (SSL)
encrypts all HTTP traffic, allowing secure access to the browser-based management GUI in the switch
- Secure FTP
allows secure file transfer to and from the switch; protects against unwanted file downloads or unauthorized copying of a switch configuration file
- Management Interface Wizard
helps secure management interfaces such as SNMP, telnet, SSH, SSL, Web, and USB at the desired level
- Switch management logon security
helps secure switch CLI logon by optionally requiring either RADIUS or TACACS+ authentication
- Security banner
displays a customized security policy when users log in to the switch

Convergence

- IP multicast routing
includes PIM Sparse and Dense modes to route IP multicast traffic
- IP multicast snooping (data-driven IGMP)
prevents flooding of IP multicast traffic
- LLDP-MED (Media Endpoint Discovery)
defines a standard extension of LLDP that stores values for parameters such as QoS and VLAN to automatically configure network devices such as IP phones
- PoE allocations
supports multiple methods (automatic, IEEE 802.3af class, LLDP-MED, or user-specified) to allocate PoE power for more efficient energy savings
- Auto VLAN configuration for voice
 - RADIUS VLAN
uses a standard RADIUS attribute and LLDP-MED to automatically configure a VLAN for IP phones
 - CDPv2
uses CDPv2 to configure legacy IP phones
- Local MAC Authentication
assigns attributes such as VLAN and QoS using locally configured profile that can be a list of MAC prefixes

Warranty and support

- Lifetime Warranty 2.0
advance hardware replacement for as long as you own the product with next-business-day delivery (available in most countries)¹
- Electronic and telephone support (for Lifetime Warranty 2.0)
limited 24x7 telephone support is available from HP for the first 3 years; limited electronic and business hours telephone support is available from HP for the entire warranty period; to reach our support centers, refer to hp.com/networking/contact-support; for details on the duration of support provided with your product purchase, refer to hp.com/networking/warrantysummary
- Software releases
to find software for your product, refer to hp.com/networking/support; for details on the software releases available with your product purchase, refer to hp.com/networking/warrantysummary

¹ HP warranty includes repair or replacement of hardware for as long as you own the product, with next business day advance replacement (available in most countries). The disk drive included with HP AllianceOne Advanced Services and Services zL Modules, HP Threat Management Services zL Module, HP AllianceOne Extended zL Module with Riverbed Steelhead, HP MSM765 zL Mobility Controller and HP Survivable Branch Communication zL Module powered by Microsoft® Lync has a five-year hardware warranty. For details, refer to the Software license and hardware warranty statements at hp.com/networking/warranty.

HP 5400R zL2 Switch Series

Specifications

	HP 5406R zL2 Switch (J9821A)	HP 5412R zL2 Switch (J9822A)	HP 5406R-44G-PoE+/2SFP+ (No PSU) v2 zL2 Switch (J9823A)
Included accessories	1 HP 5400R zL2 Management Module (J9827A) 1 HP 5406R zL2 Switch Fan Tray (J9831A)	1 HP 5400R zL2 Management Module (J9827A) 1 HP 5412R zL2 Switch Fan Tray (J9832A)	1 HP 5400R zL2 Management Module (J9827A) 1 HP 5406R zL2 Switch Fan Tray (J9831A) 1 HP 24-port Gig-T PoE+ v2 zL Module (J9534A) 1 HP 20-port Gig-T PoE+ / 2-port 10GbE SFP+ v2 zL Module (J9536A)
I/O ports and slots	6 open module slots Supports a maximum of 48 10GbE ports or 144 autosensing 10/100/1000 ports or 144 SFP ports, or a combination	12 open module slots Supports a maximum of 96 10GbE ports or 288 autosensing 10/100/1000 ports or 288 SFP ports, or a combination	44 RJ-45 autosensing 10/100/1000 PoE+ ports (IEEE 802.3 Type 10BASE-T, IEEE 802.3u Type 100BASE-TX, IEEE 802.3ab Type 1000BASE-T, IEEE 802.3at PoE+); Media Type: Auto-MDIX; Duplex: 10BASE-T/100BASE-TX: half or full; 1000BASE-T: full only 2 open 10GbE SFP+ transceiver slots 4 open module slots Supports a maximum of 34 10GbE ports or 140 autosensing 10/100/1000 ports or 98 SFP ports, or a combination
Power supplies	2 power supply slots 1 minimum power supply required (ordered separately)	4 power supply slots 2 minimum power supplies required (ordered separately)	2 power supply slots 1 minimum power supply required (ordered separately)
Fan tray	includes: 1 x J9831A 1 fan tray slot	includes: 1 x J9832A 1 fan tray slot	includes: 1 x J9831A 1 fan tray slot
Physical characteristics			
Dimensions	17.5(w) x 17.75(d) x 6.9(h) in (44.45 x 45.09 x 17.53 cm) (4U height)	17.5(w) x 17.75(d) x 12.1(h) in (44.45 x 45.09 x 30.73 cm) (7U height)	17.5(w) x 17.75(d) x 6.9(h) in (44.45 x 45.09 x 17.53 cm) (4U height)
Weight	24.5 lb (11.11 kg)	38.1 lb (17.28 kg)	28.11 lb (12.75 kg)
Memory and processor			
Gigabit module	ARM11 @ 450 MHz; packet buffer size: 18 MB internal	ARM11 @ 450 MHz; packet buffer size: 18 MB internal	ARM11 @ 450 MHz; packet buffer size: 18 MB internal
10G module	ARM11 @ 550 MHz; packet buffer size: 18 MB internal	ARM11 @ 550 MHz; packet buffer size: 18 MB internal	ARM11 @ 550 MHz; packet buffer size: 18 MB internal
Management module	Freescall P2020 dual core @ 1.2 GHz, 16 MB flash, 1 GB SD Card, 4 GB DDR3 SODIMM	Freescall P2020 dual core @ 1.2 GHz, 16 MB flash, 1 GB SD Card, 4 GB DDR3 SODIMM	Freescall P2020 dual core @ 1.2 GHz, 16 MB flash, 1 GB SD Card, 4 GB DDR3 SODIMM
Mounting and enclosure	Mounts in an EIA standard 19-inch telco rack or equipment cabinet (hardware included); horizontal surface mounting only	Mounts in an EIA standard 19-inch telco rack or equipment cabinet (hardware included); horizontal surface mounting only	Mounts in an EIA standard 19-inch telco rack or equipment cabinet (hardware included); horizontal surface mounting only

	HP 5406R z12 Switch (J9821A)	HP 5412R z12 Switch (J9822A)	HP 5406R-44G-PoE+/2SFP+ (No PSU) v2 z12 Switch (J9823A)
Performance			
1000 Mb Latency	< 2.9 μ s (FIFO 64-byte packets)	< 2.9 μ s (FIFO 64-byte packets)	< 2.9 μ s (FIFO 64-byte packets)
10 Gb/s Latency	< 2.0 μ s (FIFO 64-byte packets)	< 2.0 μ s (FIFO 64-byte packets)	< 2.0 μ s (FIFO 64-byte packets)
Throughput	392.8 Mpps	785.7 Mpps	392.8 Mpps
Routing/Switching capacity	528 Gb/s	1.0 Tb/s	528 Gb/s
Switch fabric speed	1015 Gb/s	2.0 Tb/s	1015 Gb/s
Routing table size	10000 entries (IPv4), 5000 entries (IPv6)	10000 entries (IPv4), 5000 entries (IPv6)	10000 entries (IPv4), 5000 entries (IPv6)
MAC address table size	64000 entries	64000 entries	64000 entries
Environment			
Operating temperature	32°F to 113°F (0°C to 45°C); 0°C to 40°C with J8177C transceiver installed, 0°C to 35°C with FIPS Opacity Shield installed	32°F to 113°F (0°C to 45°C); 0°C to 40°C with J8177C transceiver installed, 0°C to 35°C with FIPS Opacity Shield installed	32°F to 113°F (0°C to 45°C); 0°C to 40°C with J8177C transceiver installed, 0°C to 35°C with FIPS Opacity Shield installed
Operating relative humidity	15% to 95% @ 113°F (45°C), noncondensing	15% to 95% @ 113°F (45°C), noncondensing	15% to 95% @ 113°F (45°C), noncondensing
Nonoperating/Storage temperature	-40°F to 158°F (-40°C to 70°C)	-40°F to 158°F (-40°C to 70°C)	-40°F to 158°F (-40°C to 70°C)
Nonoperating/Storage relative humidity	15% to 95% @ 149°F (65°C), noncondensing	15% to 95% @ 149°F (65°C), noncondensing	15% to 95% @ 149°F (65°C), noncondensing
Altitude	up to 10,000 ft (3 km)	up to 10,000 ft (3 km)	up to 10,000 ft (3 km)
Acoustic	Power: 44 dB, Pressure: 31.7 dB ISO 7779, ISO 9296	Power: 49 dB, Pressure: 35.7 dB ISO 7779, ISO 9296	Power: 44 dB, Pressure: 31.7 dB ISO 7779, ISO 9296
Electrical characteristics			
Frequency	50/60 Hz	50/60 Hz	50/60 Hz
Description	Does not come with power supply. Two power supply slots are available; three different power supplies are available. See power supply products for additional specifications.	Does not come with power supply. Four power supply slots are available; three different power supplies are available. See power supply products for additional specifications.	Does not come with power supply. Two open power supply slots are available; three different power supplies are available. See power supply products for additional specifications.
Maximum heat dissipation	2450 BTU/hr (2584 kJ/hr), (max. non-PoE); 3700 BTU/hr (3903 kJ/hr) (max. using PoE)	4900 BTU/hr (5169 kJ/hr), (max. non-PoE); 7400 BTU/hr (7,807 kJ/hr) (max. using PoE)	2450 BTU/hr (2584.75 kJ/hr), (max. non-PoE); 3700 BTU/hr (3903 kJ/hr) (max. using PoE)
AC voltage	100 - 127 / 200 - 240 VAC	100 - 127 / 200 - 240 VAC	110 - 127 / 200 - 240 VAC
Idle power			215 W
Notes			
	Heat dissipation does not include heat dissipated by the PoE-powered devices themselves.	Heat dissipation does not include heat dissipated by the PoE-powered devices themselves. When more than four power cords are installed in a 5412R z12 switch chassis, additional installation requirements are needed. Refer to the HP 5400R z12 Switches Quick Setup Guide and Safety/Regulatory Information manual for details.	Idle power is the actual power consumption of the device with no ports connected. Heat dissipation does not include heat dissipated by the PoE-powered devices themselves.
Safety			
	CSA 22.2 No. 60950; UL 60950; IEC 60950; EN 60950	CSA 22.2 No. 60950; UL 60950; IEC 60950; EN 60950	CSA 22.2 No. 60950; UL 60950; IEC 60950; EN 60950
Emissions			
	FCC part 15 Class A; EN 55022/ CISPR 22 Class A	FCC part 15 Class A; EN 55022/ CISPR 22 Class A	FCC part 15 Class A; EN 55022/ CISPR 22 Class A

	HP 5406R zL2 Switch (J9821A)	HP 5412R zL2 Switch (J9822A)	HP 5406R-44G-PoE+/2SFP+ (No PSU) v2 zL2 Switch (J9823A)
Immunity			
EN	EN 55024, CISPR 24	EN 55024, CISPR 24	EN 55024, CISPR 24
ESD	IEC 61000-4-2; 4 kV CD, 8 kV AD; HP ENV. 765.002	IEC 61000-4-2; 4 kV CD, 8 kV AD; HP ENV. 765.002	IEC 61000-4-2; 4 kV CD, 8 kV AD; HP ENV. 765.002
Radiated EFT/Burst	IEC 61000-4-3; 3 V/m IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)	IEC 61000-4-3; 3 V/m IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)	IEC 61000-4-3; 3 V/m IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)
Surge	IEC 61000-4-5; 1 kV/2 kV AC, 1kV signal, 0.5 kV DC	IEC 61000-4-5; 1 kV/2 kV AC, 1kV signal, 0.5 kV DC	IEC 61000-4-5; 1 kV/2 kV AC, 1kV signal, 0.5 kV DC
Conducted Power frequency magnetic field	IEC 61000-4-6; 3 Vrms IEC 61000-4-8; 1 A/m, 50 or 60 Hz	IEC 61000-4-6; 3 Vrms IEC 61000-4-8; 1 A/m, 50 or 60 Hz	IEC 61000-4-6; 3 Vrms IEC 61000-4-8; 1 A/m, 50 or 60 Hz
Voltage dips and interruptions	IEC 61000-4-11; >95% reduction, 0.5 period; 30% reduction, 25 periods	IEC 61000-4-11; >95% reduction, 0.5 period; 30% reduction, 25 periods	IEC 61000-4-11; >95% reduction, 0.5 period; 30% reduction, 25 periods
Harmonics Flicker	EN 61000-3-2, IEC 61000-3-2 EN 61000-3-3, IEC 61000-3-3	EN 61000-3-2, IEC 61000-3-2 EN 61000-3-3, IEC 61000-3-3	EN 61000-3-2, IEC 61000-3-2 EN 61000-3-3, IEC 61000-3-3
Management	IMC—Intelligent Management Center; command-line interface; Web browser; configuration menu; out-of-band management (RJ-45 Ethernet); SNMP Manager; out-of-band management (serial RS-232C or Micro USB)	IMC—Intelligent Management Center; command-line interface; Web browser; configuration menu; out-of-band management (RJ-45 Ethernet); SNMP Manager; out-of-band management (serial RS-232C or Micro USB)	IMC—Intelligent Management Center; command-line interface; Web browser; configuration menu; out-of-band management (RJ-45 Ethernet); SNMP Manager; out-of-band management (serial RS-232C or Micro USB)
Notes	Supported 1G SFP transceivers are revision “B” or later (product number ends with the letter “B” or later; for example, J9142B, J8177C)	Supported 1G SFP transceivers are revision “B” or later (product number ends with the letter “B” or later; for example, J9142B, J8177C)	Supported 1G SFP transceivers are revision “B” or later (product number ends with the letter “B” or later; for example, J9142B, J8177C)
Services	Refer to the HP website at hp.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local HP sales office.	Refer to the HP website at hp.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local HP sales office.	Refer to the HP website at hp.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local HP sales office.

HP 5400R zL2 Switch Series

Specifications (continued)

	HP 5412R-92G-PoE+/2SFP+ (No PSU) v2 zL2 Switch (J9825A)	HP 5406R-44G-PoE+/4SFP (No PSU) v2 zL2 Switch (J9824A)
Included accessories	1 HP 5400R zL2 Management Module (J9827A) 1 HP 5412R zL2 Switch Fan Tray (J9832A) 3 HP 24-port Gig-T PoE+ v2 zL Module (J9534A) 1 HP 20-port Gig-T PoE+ / 2-port 10GbE SFP+ v2 zL Module (J9536A)	1 HP 5400R zL2 Management Module (J9827A) 1 HP 5406R zL2 Switch Fan Tray (J9831A) 1 HP 24-port Gig-T PoE+ v2 zL Module (J9534A) 1 HP 20-port Gig-T PoE+ / 4-port SFP v2 zL Module (J9535A)
I/O ports and slots	92 RJ-45 autosensing 10/100/1000 PoE+ ports (IEEE 802.3 Type 10BASE-T, IEEE 802.3u Type 100BASE-TX, IEEE 802.3ab Type 1000BASE-T, IEEE 802.3at PoE+); Media Type: Auto-MDIX; Duplex: 10BASE-T/100BASE-TX: half or full; 1000BASE-T: full only 2 open 10GbE SFP+ transceiver slots 8 open module slots Supports a maximum of 66 10GbE ports or 284 autosensing 10/100/1000 ports or 194 SFP ports, or a combination	44 RJ-45 autosensing 10/100/1000 ports (IEEE 802.3 Type 10BASE-T, IEEE 802.3u Type 100BASE-TX, IEEE 802.3ab Type 1000BASE-T); Media Type: Auto-MDIX; Duplex: 10BASE-T/100BASE-TX: half or full; 1000BASE-T: full only 4 open SFP transceiver slots 4 open module slots Supports a maximum of 32 10GbE ports or 140 autosensing 10/100/1000 ports or 100 SFP ports, or a combination
Power supplies	4 power supply slots 2 minimum power supplies required (ordered separately)	2 power supply slots 1 minimum power supply required (ordered separately)
Fan tray	includes: 1 x J9832A 1 fan tray slot	includes: 1 x J9831A 1 fan tray slot
Physical characteristics		
Dimensions	17.5(w) x 17.75(d) x 12.1(h) in (44.45 x 45.09 x 30.73 cm) (7U height)	17.5(w) x 17.75(d) x 6.9(h) in (44.45 x 45.09 x 17.53 cm) (4U height)
Weight	45.19 lb (20.5 kg)	26.19 lb (11.88 kg)
Memory and processor		
Gigabit module	ARM11 @ 450 MHz; packet buffer size: 18 MB internal	ARM11 @ 450 MHz; packet buffer size: 18 MB internal
10G module	ARM11 @ 550 MHz; packet buffer size: 18 MB internal	ARM11 @ 550 MHz; packet buffer size: 18 MB internal
Management module	Freescale P2020 dual core @ 1.2 MHz, 16 MB flash, 1 GB SD Card, 4 GB DDR3 SODIMM	Freescale P2020 dual core @ 1.2 GHz, 16 MB flash, 1 GB SD Card, 4 GB DDR3 SODIMM
Mounting and enclosure	Mounts in an EIA standard 19-inch telco rack or equipment cabinet (hardware included); horizontal surface mounting only	Mounts in an EIA standard 19-inch telco rack or equipment cabinet (hardware included); horizontal surface mounting only
Performance		
1000 Mb Latency	< 2.9 μ s (FIFO 64-byte packets)	< 2.9 μ s (FIFO 64-byte packets)
10 Gb/s Latency	< 2.0 μ s (FIFO 64-byte packets)	< 2.0 μ s (FIFO 64-byte packets)
Throughput	785.7 Mpps	392.8 Mpps
Routing/Switching capacity	1.0 Tb/s	528 Gb/s
Switch fabric speed	2.0 Tb/s	1015 Gb/s
Routing table size	10000 entries (IPv4), 5000 entries (IPv6)	10000 entries (IPv4), 5000 entries (IPv6)
MAC address table size	64000 entries	64000 entries

	HP 5412R-92G-PoE+/2SFP+ (No PSU) v2 zL2 Switch (J9825A)	HP 5406R-44G-PoE+/4SFP (No PSU) v2 zL2 Switch (J9824A)
Environment		
Operating temperature	32°F to 113°F (0°C to 45°C); 0°C to 40°C with J8177C transceiver installed, 0°C to 35°C with FIPS Opacity Shield installed	32°F to 113°F (0°C to 45°C); 0°C to 40°C with J8177C transceiver installed, 0°C to 35°C with FIPS Opacity Shield installed
Operating relative humidity	15% to 95% @ 113°F (45°C), noncondensing	15% to 95% @ 113°F (45°C), noncondensing
Nonoperating/Storage temperature	-40°F to 158°F (-40°C to 70°C)	-40°F to 158°F (-40°C to 70°C)
Nonoperating/Storage relative humidity	15% to 95% @ 149°F (65°C), noncondensing	15% to 95% @ 149°F (65°C), noncondensing
Altitude	up to 10,000 ft (3 km)	up to 10,000 ft (3 km)
Acoustic	Power: 49 dB, Pressure: 35.7 dB ISO 7779, ISO 9296	Power: 44 dB, Pressure: 31.7 dB ISO 7779, ISO 9296
Electrical characteristics		
Frequency	50/60 Hz	50/60 Hz
Description	Does not come with power supply. Four open power supply slots are available; three different power supplies are available. See power supply products for additional specifications.	Does not come with power supply. Two open power supply slots are available; three different power supplies are available. See power supply products for additional specifications.
Maximum heat dissipation	4900 BTU/hr (5169.5 kJ/hr), (max. non-PoE); 7400 BTU/hr (7807 kJ/hr) (max. using PoE)	2450 BTU/hr (2584.75 kJ/hr), (max. non-PoE); 3700 BTU/hr (3903 kJ/hr) (max. using PoE)
AC voltage	110 - 127 / 200 - 240 VAC	110 - 127 / 200 - 240 VAC
Idle power	312 W	215 W
Notes		
	Idle power is the actual power consumption of the device with no ports connected. Heat dissipation does not include heat dissipated by the PoE-powered devices themselves. When more than four power cords are installed in a 5412R zL2 switch chassis, additional installation requirements are needed. Refer to the HP 5400R zL2 Switches Quick Setup Guide and Safety/Regulatory Information manual for details.	Idle power is the actual power consumption of the device with no ports connected. Heat dissipation does not include heat dissipated by the PoE-powered devices themselves.
Safety		
	CSA 22.2 No. 60950; UL 60950; IEC 60950; EN 60950	CSA 22.2 No. 60950; UL 60950; IEC 60950; EN 60950
Emissions		
	FCC part 15 Class A; EN 55022/CISPR 22 Class A	FCC part 15 Class A; EN 55022/CISPR 22 Class A

	HP 5412R-92G-PoE+/2SFP+ (No PSU) v2 zL2 Switch (J9825A)	HP 5406R-44G-PoE+/4SFP (No PSU) v2 zL2 Switch (J9824A)
Immunity		
EN	EN 55024, CISPR 24	EN 55024, CISPR 24
ESD	IEC 61000-4-2; 4 kV CD, 8 kV AD; HP ENV. 765.002	IEC 61000-4-2; 4 kV CD, 8 kV AD; HP ENV. 765.002
Radiated	IEC 61000-4-3; 3 V/m	IEC 61000-4-3; 3 V/m
EFT/Burst	IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)	IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)
Surge	IEC 61000-4-5; 1 kV/2 kV AC, 1kV signal, 0.5 kV DC	IEC 61000-4-5; 1 kV/2 kV AC, 1kV signal, 0.5 kV DC
Conducted	IEC 61000-4-6; 3 Vrms	IEC 61000-4-6; 3 Vrms
Power frequency magnetic field	IEC 61000-4-8; 1 A/m, 50 or 60 Hz	IEC 61000-4-8; 1 A/m, 50 or 60 Hz
Voltage dips and interruptions	IEC 61000-4-11; >95% reduction, 0.5 period; 30% reduction, 25 periods	IEC 61000-4-11; >95% reduction, 0.5 period; 30% reduction, 25 periods
Harmonics	EN 61000-3-2, IEC 61000-3-2	EN 61000-3-2, IEC 61000-3-2
Flicker	EN 61000-3-3, IEC 61000-3-3	EN 61000-3-3, IEC 61000-3-3
Management	IMC—Intelligent Management Center; command-line interface; Web browser; configuration menu; out-of-band management (RJ-45 Ethernet); SNMP Manager; out-of-band management (serial RS-232C or Micro USB)	IMC—Intelligent Management Center; command-line interface; Web browser; configuration menu; out-of-band management (RJ-45 Ethernet); SNMP Manager; out-of-band management (serial RS-232C or Micro USB)
Notes	Supported 1G SFP transceivers are revision "B" or later (product number ends with the letter "B" or later; for example, J9142B, J8177C).	Supported 1G SFP transceivers are revision "B" or later (product number ends with the letter "B" or later; for example, J9142B, J8177C).
Services	Refer to the HP website at hp.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local HP sales office.	Refer to the HP website at hp.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local HP sales office.

HP 5400R zL2 Switch Series

Specifications (continued)

	HP 5412R-92G-PoE+/4SFP (No PSU) v2 zL2 Switch (J9826A)	HP 5406R-8XGT/8SFP+ (No PSU) v2 zL2 Switch (J9868A)
Included accessories	1 HP 5400R zL2 Management Module (J9827A) 1 HP 5412R zL2 Switch Fan Tray (J9832A) 3 HP 24-port Gig-T PoE+ v2 zL Module (J9534A) 1 HP 20-port Gig-T PoE+ / 4-port SFP v2 zL Module (J9535A)	1 HP 5400R zL2 Management Module (J9827A) 1 HP 5406R zL2 Switch Fan Tray (J9831A) 1 HP 8-port 10GbE SFP+ v2 zL Module (J9538A) 1 HP 8-port 10GBASE-T v2 zL Module (J9546A)
I/O ports and slots	92 RJ-45 autosensing 10/100/1000 PoE+ ports (IEEE 802.3 Type 10BASE-T, IEEE 802.3u Type 100BASE-TX, IEEE 802.3ab Type 1000BASE-T, IEEE 802.3at PoE+); Media Type: Auto-MDIX; Duplex: 10BASE-T/100BASE-TX: half or full; 1000BASE-T: full only 4 open SFP transceiver slots 8 open module slots Supports a maximum of 64 10GbE ports or 284 autosensing 10/100/1000 ports or 196 SFP ports, or a combination	8 RJ-45 10GbE ports (IEEE 802.3an-2006 Type 10GBASE-T) 8 open 10GbE SFP+ transceiver slots 4 open module slots Supports a maximum of 32 10GbE ports or 96 autosensing 10/100/1000 ports or 96 SFP ports, or a combination
Power supplies	4 power supply slots 2 minimum power supplies required (ordered separately)	2 power supply slots 1 minimum power supply required (ordered separately)
Fan tray	includes: 1 x J9832A 1 fan tray slot	includes: 1 x J9831A 1 fan tray slot
Physical characteristics		
Dimensions	17.5(w) x 17.75(d) x 12.1(h) in (44.45 x 45.09 x 30.73 cm) (7U height)	17.5(w) x 17.75(d) x 6.9(h) in (44.45 x 45.09 x 17.53 cm) (4U height)
Weight	45.4 lb (20.59 kg)	28.11 lb (12.75 kg)
Memory and processor		
Gigabit module	ARM11 @ 450 MHz; packet buffer size: 18 MB internal	ARM11 @ 550 MHz; packet buffer size: 18 MB internal
10G module	ARM11 @ 550 MHz; packet buffer size: 18 MB internal	ARM11 @ 550 MHz; packet buffer size: 18 MB internal
Management module	Freescale P2020 dual core @ 1.2 GHz, 16 MB flash, 1 GB SD Card, 4 GB DDR3 SODIMM	Freescale P2020 dual core @ 1.2 GHz, 16 MB flash, 1 GB SD Card, 4 GB DDR3 SODIMM
Mounting and enclosure	Mounts in an EIA standard 19-inch telco rack or equipment cabinet (hardware included); horizontal surface mounting only	Mounts in an EIA standard 19-inch telco rack or equipment cabinet (hardware included); horizontal surface mounting only
Performance		
1000 Mb Latency	< 2.9 μ s (FIFO 64-byte packets)	< 2.9 μ s (FIFO 64-byte packets)
10 Gb/s Latency	< 2.0 μ s (FIFO 64-byte packets)	< 2.0 μ s (FIFO 64-byte packets)
Throughput	785.7 Mpps	392.8 Mpps
Routing/Switching capacity	1.0 Tb/s	528 Gb/s
Switch fabric speed	2.0 Tb/s	1015 Gb/s
Routing table size	10000 entries (IPv4), 5000 entries (IPv6)	10000 entries (IPv4), 5000 entries (IPv6)
MAC address table size	64000 entries	64000 entries

	HP 5412R-92G-PoE+/4SFP (No PSU) v2 zL2 Switch (J9826A)	HP 5406R-8XGT/8SFP+ (No PSU) v2 zL2 Switch (J9868A)
Environment		
Operating temperature	32°F to 113°F (0°C to 45°C); 0°C to 40°C with J8177C transceiver installed, 0°C to 35°C with FIPS Opacity Shield installed	32°F to 113°F (0°C to 45°C); 0°C to 40°C with J8177C transceiver installed, 0°C to 35°C with FIPS Opacity Shield installed
Operating relative humidity	15% to 95% @ 113°F (45°C), noncondensing	15% to 95% @ 113°F (45°C), noncondensing
Nonoperating/Storage temperature	-40°F to 158°F (-40°C to 70°C)	-40°F to 158°F (-40°C to 70°C)
Nonoperating/Storage relative humidity	15% to 95% @ 149°F (65°C), noncondensing	15% to 95% @ 149°F (65°C), noncondensing
Altitude	up to 10,000 ft (3 km)	up to 10,000 ft (3 km)
Acoustic	Power: 49 dB, Pressure: 35.7 dB ISO 7779, ISO 9296	Power: 44 dB, Pressure: 31.7 dB ISO 7779, ISO 9296
Electrical characteristics		
Frequency	50/60 Hz	50/60 Hz
Description	Does not come with power supply. Four open power supply slots are available; three different power supplies are available. See power supply products for additional specifications.	Does not come with power supply. Two open power supply slots are available; three different power supplies are available. See power supply products for additional specifications.
Maximum heat dissipation	4900 BTU/hr (5169.5 kJ/hr), (max. non-PoE); 7400 BTU/hr (7807 kJ/hr) (max. using PoE)	2450 BTU/hr (2584.75 kJ/hr), (max. non-PoE); 3700 BTU/hr (3903 kJ/hr) (max. using PoE)
AC voltage	110 - 127 / 200 - 240 VAC	110 - 127 / 200 - 240 VAC
Idle power	312 W	215 W
Notes		
	Idle power is the actual power consumption of the device with no ports connected. Heat dissipation does not include heat dissipated by the PoE-powered devices themselves. When more than four power cords are installed in a 5412R zL2 switch chassis, additional installation requirements are needed. Refer to the HP 5400R zL2 Switches Quick Setup Guide and Safety/Regulatory Information manual for details.	Idle power is the actual power consumption of the device with no ports connected. Heat dissipation does not include heat dissipated by the PoE-powered devices themselves.
Safety		
	CSA 22.2 No. 60950; UL 60950; IEC 60950; EN 60950	CSA 22.2 No. 60950; UL 60950; IEC 60950; EN 60950
Emissions		
	FCC part 15 Class A; EN 55022/CISPR 22 Class A	FCC part 15 Class A; EN 55022/CISPR 22 Class A

	HP 5412R-92G-PoE+/4SFP (No PSU) v2 z12 Switch (J9826A)	HP 5406R-8XGT/8SFP+ (No PSU) v2 z12 Switch (J9868A)
Immunity		
EN	EN 55024, CISPR 24	EN 55024, CISPR 24
ESD	IEC 61000-4-2; 4 kV CD, 8 kV AD; HP ENV. 765.002	IEC 61000-4-2; 4 kV CD, 8 kV AD; HP ENV. 765.002
Radiated	IEC 61000-4-3; 3 V/m	IEC 61000-4-3; 3 V/m
EFT/Burst	IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)	IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)
Surge	IEC 61000-4-5; 1 kV/2 kV AC, 1kV signal, 0.5 kV DC	IEC 61000-4-5; 1 kV/2 kV AC, 1kV signal, 0.5 kV DC
Conducted	IEC 61000-4-6; 3 Vrms	IEC 61000-4-6; 3 Vrms
Power frequency magnetic field	IEC 61000-4-8; 1 A/m, 50 or 60 Hz	IEC 61000-4-8; 1 A/m, 50 or 60 Hz
Voltage dips and interruptions	IEC 61000-4-11; >95% reduction, 0.5 period; 30% reduction, 25 periods	IEC 61000-4-11; >95% reduction, 0.5 period; 30% reduction, 25 periods
Harmonics	EN 61000-3-2, IEC 61000-3-2	EN 61000-3-2, IEC 61000-3-2
Flicker	EN 61000-3-3, IEC 61000-3-3	EN 61000-3-3, IEC 61000-3-3
Management	IMC—Intelligent Management Center; command-line interface; Web browser; configuration menu; out-of-band management (RJ-45 Ethernet); SNMP Manager; out-of-band management (serial RS-232C or Micro USB)	IMC—Intelligent Management Center; command-line interface; Web browser; configuration menu; out-of-band management (RJ-45 Ethernet); SNMP Manager; out-of-band management (serial RS-232C or Micro USB)
Notes	Supported 1G SFP transceivers are revision “B” or later (product number ends with the letter “B” or later; for example, J9142B, J8177C).	Supported 1G SFP transceivers are revision “B” or later (product number ends with the letter “B” or later; for example, J9142B, J8177C).
Services	Refer to the HP website at hp.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local HP sales office.	Refer to the HP website at hp.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local HP sales office.

Standards and Protocols

(applies to all products in series)

BGP	RFC 1997 BGP Communities Attribute RFC 2918 Route Refresh Capability RFC 4271 A Border Gateway Protocol 4 (BGP-4)	RFC 4456 BGP Route Reflection: An Alternative to Full Mesh Internal BGP (IBGP)	RFC 5492 Capabilities Advertisement with BGP-4
Device management	RFC 1591 DNS (client)	HTML and telnet management	
General protocols	IEEE 802.1ad Q-in-Q IEEE 802.1AX-2008 Link Aggregation IEEE 802.1D MAC Bridges IEEE 802.1p Priority IEEE 802.1Q VLANs IEEE 802.1s Multiple Spanning Trees IEEE 802.1v VLAN classification by Protocol and Port IEEE 802.1w Rapid Reconfiguration of Spanning Tree IEEE 802.3ad Link Aggregation Control Protocol (LACP) IEEE 802.3af Power over Ethernet IEEE 802.3x Flow Control	RFC 768 UDP RFC 783 TFTP Protocol (revision 2) RFC 792 ICMP RFC 793 TCP RFC 826 ARP RFC 854 TELNET RFC 868 Time Protocol RFC 951 BOOTP RFC 1058 RIPv1 RFC 1350 TFTP Protocol (revision 2) RFC 1519 CIDR	RFC 1542 BOOTP Extensions RFC 2030 Simple Network Time Protocol (SNTP) v4 RFC 2131 DHCP RFC 2453 RIPv2 RFC 2548 (MS-RAS-Vendor only) RFC 3046 DHCP Relay Agent Information Option RFC 3576 Ext to RADIUS (CoA only) RFC 3768 VRRP RFC 4675 RADIUS VLAN & Priority UDLD (Uni-directional Link Detection)
IP multicast	RFC 3376 IGMPv3 (host joins only)	RFC 3973 PIM Dense Mode	RFC 4601 PIM Sparse Mode
IPv6	RFC 1981 IPv6 Path MTU Discovery RFC 2375 IPv6 Multicast Address Assignments RFC 2460 IPv6 Specification RFC 2464 Transmission of IPv6 over Ethernet Networks RFC 2710 Multicast Listener Discovery (MLD) for IPv6 RFC 2925 Definitions of Managed Objects for Remote Ping, Traceroute, and Lookup Operations (Ping only) 3019 MLDv1 MIB RFC 3315 DHCPv6 (client and relay) RFC 3484 Default Address Selection for IPv6 RFC 3587 IPv6 Global Unicast Address Format RFC 3596 DNS Extension for IPv6	RFC 3810 MLDv2 for IPv6 RFC 4022 MIB for TCP RFC 4087 IP Tunnel MIB RFC 4113 MIB for UDP RFC 4213 Basic Transition Mechanisms for IPv6 Hosts and Routers RFC 4251 SSHv6 Architecture RFC 4252 SSHv6 Authentication RFC 4253 SSHv6 Transport Layer RFC 4254 SSHv6 Connection RFC 4291 IP Version 6 Addressing Architecture RFC 4293 MIB for IP	RFC 4294 IPv6 Node Requirements RFC 4419 Key Exchange for SSH RFC 4443 ICMPv6 RFC 4541 IGMP & MLD Snooping Switch RFC 4861 IPv6 Neighbor Discovery RFC 4862 IPv6 Stateless Address Auto-configuration RFC 5095 Deprecation of Type 0 Routing Headers in IPv6 RFC 5340 OSPFv3 for IPv6 RFC 5453 Reserved IPv6 Interface Identifiers RFC 5519 Multicast Group Membership Discovery MIB (MLDv2 only) RFC 5722 Handling of Overlapping IPv6 Fragments

Standards and Protocols

(applies to all products in series)

MIBs	IEEE 802.1ap (MSTP and STP MIB's only) RFC 1213 MIB II RFC 1493 Bridge MIB RFC 1724 RIPv2 MIB RFC 1850 OSPFv2 MIB RFC 2021 RMONv2 MIB	RFC 2096 IP Forwarding Table MIB RFC 2613 SMON MIB RFC 2618 RADIUS Client MIB RFC 2620 RADIUS Accounting MIB RFC 2665 Ethernet-Like-MIB RFC 2668 802.3 MAU MIB	RFC 2674 802.1p and IEEE 802.1Q Bridge MIB RFC 2737 Entity MIB (Version 2) RFC 2787 VRRP MIB RFC 2863 The Interfaces Group MIB RFC 2925 Ping MIB RFC 2933 IGMP MIB
Network management	IEEE 802.1AB Link Layer Discovery Protocol (LLDP) RFC 2819 Four groups of RMON: 1 (statistics), 2 (history), 3 (alarm) and 9 (events)	RFC 3176 sFlow ANSI/TIA-1057 LLDP Media Endpoint Discovery (LLDP-MED)	SNMPv1/v2c/v3 XRMON
OSPF	RFC 2328 OSPFv2	RFC 3101 OSPF NSSA	RFC 5340 OSPFv3 for IPv6
QoS/CoS	RFC 2474 DiffServ Precedence, including 8 queues/port	RFC 2597 DiffServ Assured Forwarding (AF)	RFC 2598 DiffServ Expedited Forwarding (EF)
Security	IEEE 802.1X Port Based Network Access Control RFC 1492 TACACS+ RFC 2865 RADIUS (client only)	RFC 2866 RADIUS Accounting RFC 3579 RADIUS Support For Extensible Authentication Protocol (EAP)	Secure Sockets Layer (SSL) SSHv2 Secure Shell

HP 5400R zL2 Switch Series accessories

Modules

HP 8-port 10GBASE-T v2 zL Module (J9546A)
 HP 8-port 10GbE SFP+ v2 zL Module (J9538A)
 HP 20-port Gig-T PoE+ / 2-port 10GbE SFP+ v2 zL Module (J9536A)
 HP 20-port Gig-T PoE+ / 4-port SFP v2 zL Module (J9535A)
 HP 24-port SFP v2 zL Module (J9537A)
 HP 12-port Gig-T PoE+ / 12-port SFP v2 zL Module (J9637A)
 HP 24-port Gig-T PoE+ v2 zL Module (J9534A)
 HP 24-port 10/100 PoE+ v2 zL Module (J9547A)
 HP 24-port Gig-T v2 zL Module (J9550A)
 HP 20-port Gig-T / 4-port SFP v2 zL Module (J9549A)
 HP 20-port Gig-T / 2-port 10GbE SFP+ v2 zL Module (J9548A)
 HP Advanced Services v2 zL Module with HDD (J9857A)
 HP Advanced Services v2 zL Module with SSD (J9858A)
New HP 5400R zL2 Management Module (J9827A)

Transceivers

HP X131 10G X2 SC ER Transceiver (J8438A)
 HP X131 10G X2 SC SR Transceiver (J8436A)
 HP X131 10G X2 CX4 Transceiver (J8440C)
 HP X111 100M SFP LC FX Transceiver (J9054C)
 HP X131 10G X2 SC LR Transceiver (J8437A)
 HP X131 10G X2 SC LRM Transceiver (J9144A)
 HP X112 100M SFP LC BX-D Transceiver (J9099B)
 HP X112 100M SFP LC BX-U Transceiver (J9100B)
 HP X132 10G SFP+ LC SR Transceiver (J9150A)
 HP X132 10G SFP+ LC LR Transceiver (J9151A)
 HP X132 10G SFP+ LC LRM Transceiver (J9152A)
 HP X121 1G SFP LC LH Transceiver (J4860C)
 HP X121 1G SFP LC SX Transceiver (J4858C)
 HP X121 1G SFP LC LX Transceiver (J4859C)
 HP X121 1G SFP RJ45 T Transceiver (J8177C)
 HP X122 1G SFP LC BX-D Transceiver (J9142B)
 HP X122 1G SFP LC BX-U Transceiver (J9143B)
 HP X132 10G SFP+ LC ER Transceiver (J9153A)

Cables

HP X242 10G SFP+ to SFP+ 1m Direct Attach Copper Cable (J9281B)
 HP X242 10G SFP+ to SFP+ 3m Direct Attach Copper Cable (J9283B)
 HP X242 10G SFP+ to SFP+ 7m Direct Attach Copper Cable (J9285B)
 HP X244 10G XFP to SFP+ 1m Direct Attach Copper Cable (J9300A)
 HP X244 10G XFP to SFP+ 3m Direct Attach Copper Cable (J9301A)
 HP X244 10G XFP to SFP+ 5m Direct Attach Copper Cable (J9302A)
 HP 0.5 m Multimode OM3 LC/LC Optical Cable (AJ833A)
 HP 1 m Multimode OM3 LC/LC Optical Cable (AJ834A)
 HP 2 m Multimode OM3 LC/LC Optical Cable (AJ835A)
 HP 5 m Multimode OM3 LC/LC Optical Cable (AJ836A)
 HP 15 m Multimode OM3 LC/LC Optical Cable (AJ837A)
 HP 30 m Multimode OM3 LC/LC Optical Cable (AJ838A)
 HP 50 m Multimode OM3 LC/LC Optical Cable (AJ839A)
 HP Premier Flex LC/LC Multi-mode OM4 2 fiber 1m Cable (QK732A)
 HP Premier Flex LC/LC Multi-mode OM4 2 fiber 2m Cable (QK733A)
 HP Premier Flex LC/LC Multi-mode OM4 2 fiber 5m Cable (QK734A)
 HP Premier Flex LC/LC Multi-mode OM4 2 fiber 15m Cable (QK735A)
 HP Premier Flex LC/LC Multi-mode OM4 2 fiber 30m Cable (QK736A)
 HP Premier Flex LC/LC Multi-mode OM4 2 fiber 50m Cable (QK737A)
 HP X242 10G SFP+ to SFP+ 10m Direct Attach Copper Cable (J9286B)
 HP X242 10G SFP+ to SFP+ 15m Direct Attach Copper Cable (J9287B)

HP 5400R zL2 Switch Series accessories (continued)

Power Supply	<p>New HP 5400R 700W PoE+ zL2 Power Supply (J9828A)</p> <p>New HP 5400R 1100W PoE+ zL2 Power Supply (J9829A)</p> <p>New HP 5400R 2750W PoE+ zL2 Power Supply (J9830A)</p>
Mounting Kit	New HP X450 4U/7U Universal 4-Post Rack Mounting Kit (J9852A)
License	<p>HP MSM Additional 40 Access Point License (J9371A)</p> <p>HP MSM Additional 40 Access Point E-LTU (J9371AAE)</p>
WLAN	HP MSM775 zL Premium Controller Module (J9840A)
HP 5406R zL2 Switch (J9821A)	New HP 5406R zL2 Switch Fan Tray (J9831A)
HP 5412R zL2 Switch (J9822A)	New HP 5412R zL2 Switch Fan Tray (J9832A)
HP 5406R-44G-PoE+/2SFP+ (No PSU) v2 zL2 Switch (J9823A)	New HP 5406R zL2 Switch Fan Tray (J9831A)
HP 5412R-92G-PoE+/2SFP+ (No PSU) v2 zL2 Switch (J9825A)	New HP 5412R zL2 Switch Fan Tray (J9832A)
HP 5406R-44G-PoE+/4SFP (No PSU) v2 zL2 Switch (J9824A)	New HP 5406R zL2 Switch Fan Tray (J9831A)
HP 5412R-92G-PoE+/4SFP (No PSU) v2 zL2 Switch (J9826A)	New HP 5412R zL2 Switch Fan Tray (J9832A)
HP 5406R-8XGT/8SFP+ (No PSU) v2 zL2 Switch (J9868A)	New HP 5406R zL2 Switch Fan Tray (J9831A)

Learn more at
hp.com/networking

Sign up for updates
hp.com/go/getupdated



Share with colleagues



Rate this document

© Copyright 2014 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft is a U.S. registered trademark of the Microsoft group of companies.

4AA5-2605ENW, July 2014, Rev. 1

