

## Thread cutting tool set M3 to M12 HSS through hole/blind hole ≤ 1xD

For universal use up to 1000 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

for producing **metric (M)** male and female threads by hand in blind holes and through holes, in steel, non-ferrous metals and (cast-iron) material groups up to a strength of 1000 N/mm<sup>2</sup>.

### Execution:

- Hand tap sets, HSS, comprising taper tap with one ring (Type A), second tap with two rings (Type D) and third tap (plug) (Type C) and die with tap wrench and thread gauge

### Advantage:

- Standard geometry with very good price/performance ratio



<b>Art. no.</b>	<b>13399 312</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	13399312
<b>Thread type</b>	Metric thread
<b>Hole type</b>	Clearance/blind hole ≤ 1xD
<b>Cutting material</b>	HSS
<b>Composition of set</b>	3 hand taps for each size (taper tap/second tap/third tap (plug)) and 1 die for each size M3/M4/M5/M6/M8/M10/M12
<b>Gross Weight</b>	3.700 kg
<b>Product Group</b>	1DC

### EAN

4039247071678