

Drawer cabinets

Mobile with a pair of roller carriers and nylon rollers Ø 100 mm

Application:

For day-to-day heavy-duty use in workshops

Execution:

- All drawers with full extension
- Individual drawer lock as standard feature to prevent the cabinet from tipping over
- Perforated, slotted drawers provide a secure hold
- Very robust construction for a wide variety of applications and very demanding requirements

Advantage:

- Optimum wall height to keep items from falling out and getting lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to the lack of crossbars on the differential extension slide
- Full extension - clear view and optimal access

Delivery:

1 anti-roll-off edging, 4-sided, 1 sliding rod, 1 roller carrier pair with nylon rollers, Ø 100 mm



Art. no.	50300 819
Brand	LISTA
Manufacturer Part Number	70.023.010
Number of drawers	5 PCS
Height	890 mm
Width	411 mm
Depth	725 mm
Height x width x depth	890 x 411 x 725 mm
Housing height	700 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	300 x 600 mm
Load-carrying capacity per drawer	75 kg
Drawer lock	Single lock right
Drawer front height	2 x 75 mm, 3 x 150 mm
Cabinet colour	Light blue RAL 5012
Colour of front	Light blue RAL 5012
Cabinet equipment	Pair of castors
With sliding handle	Yes
Height of roller carrier pair	137 mm
Wheel diameter	100 mm
Material of wheel	Nylon (polyamide)
Information about the direction	Along
Load-carrying capacity of roller	400 kg
Opening/closing system	RFID Lock
Rim height	53 mm
Clear height	600 mm
LISTA unit	18 x 36 E
Gross Weight	94.000 kg
Product Group	5AN