



### Round



A = Width mm  
B = Thickness mm  
C = Length mm

Model	A	B	C	PU	Order No.
<b>LT 1</b> 	0.25		13.0	1	T005 44 435 99
10				T005 44 435 10	
100				T005 44 401 11	
<b>LT 1A</b> 	0.5		13.0	1	T005 44 489 99
10				T005 44 489 10	
100				T005 44 489 11	
<b>LT 1S</b> 	0.2		15	1	T005 44 436 99
1				T005 44 436 10	
100				T005 44 402 11	
<b>LT 1SA</b> 	0.5		15	1	T005 44 488 99
10					
100					
<b>LT 1SLX 30°</b> 	0.4		22	1	T005 44 426 99
10				T005 44 426 10	

Model	A	B	C	PU	Order No.
<b>LT 1SNW</b> 	0.1		15	1	T005 44 496 99
<b>LT 1X 30°</b> 	0.4		13.0	10	T005 44 425 10
				1	T005 44 425 99
<b>LT AS</b> 	1.6		13.0	1	T005 44 404 99
				10	T005 44 404 10
				100	T005 44 404 11
<b>LT BS</b> 	2.0		21	1	T005 44 499 99
				1	T005 44 499 10
<b>LT CS</b> 	3.2		13.0	1	T005 44 411 99
				10	T005 44 411 10

### Sloped



A = Width mm  
B = Thickness mm  
C = Length mm

Model	A	B	C	PU	Order No.
<b>LT 11CP</b> 	1.2		15	1	T005 44 421 71
<b>LT 22CP</b> 	2.0		20	1	T005 44 408 73
<b>LT 33CP</b> 	3.0		20	1	T005 44 408 77
<b>LT 4</b> 	1.2		15	1	T005 44 439 99
				10	T005 44 439 10
				100	T005 44 421 11
<b>LT 44CP</b> 	4		20	1	T005 44 408 81
<b>LT AA 60°</b> 	1.6		13.0	1	T005 44 487 99
				10	T005 44 487 10

Model	A	B	C	PU	Order No.
<b>LT BB 45</b> 	2.4		17	1	T005 44 484 99
<b>LT BB 60</b> 	2.4		17	1	T005 44 444 99
				10	T005 44 444 10
<b>LT CC 45</b> 	3.2		17	1	T005 44 485 89
<b>LT CC 60</b> 	3.2		17	1	T005 44 445 99
				10	T005 44 445 10
<b>LT DD 45</b> 	4		20	1	T005 44 478 99
				10	T005 44 478 10
<b>LT DD 45</b> 	4.6		17	1	T005 44 486 99
				10	T005 44 486 10
<b>LT F</b> 	1.2		13.0	1	T005 44 408 99
				10	T005 44 408 10
				100	T005 44 408 11