

## Data sheet

### CP 240, RS422/485 (240-1CA21)

#### Technical data

<b>Order no.</b>	<b>240-1CA21</b>
Type	CP 240, RS422/485
<b>General information</b>	
Note	-
Features	RS422/485 interface
<b>Current consumption/power loss</b>	
Current consumption from backplane bus	150 mA
Power loss	0.75 W
<b>Status information, alarms, diagnostics</b>	
Status display	yes
Interrupts	no
Process alarm	no
Diagnostic interrupt	no
Diagnostic functions	no
Diagnostics information read-out	possible
Supply voltage display	yes
Group error display	red LED
Channel error display	none
<b>Functionality Sub-D interfaces</b>	
Type	-
Type of interface	RS422/485
Connector	Sub-D, 9-pin, female
Electrically isolated	✓
MPI	-
MP2I (MPI/RS232)	-
Point-to-point interface	✓
<b>Point-to-point communication</b>	
PtP communication	✓
Interface isolated	✓
RS232 interface	-
RS422 interface	✓
RS485 interface	✓
Connector	Sub-D, 9-pin, female
Transmission speed, min.	150 bit/s
Transmission speed, max.	115.2 kbit/s
Cable length, max.	1200 m
<b>Point-to-point protocol</b>	

ASCII protocol	✓
STX/ETX protocol	✓
3964(R) protocol	✓
RK512 protocol	✓
USS master protocol	-
Modbus master protocol	✓
Modbus slave protocol	✓
Special protocols	-

#### Datasizes

Input bytes	16
Output bytes	16
Parameter bytes	16
Diagnostic bytes	0

#### Housing

Material	PPE
Mounting	Profile rail 35 mm

#### Mechanical data

Dimensions (WxHxD)	25.4 mm x 76 mm x 78 mm
Weight	80 g

#### Environmental conditions

Operating temperature	0 °C to 60 °C
Storage temperature	-25 °C to 70 °C

#### Certifications

UL508 certification	yes
---------------------	-----