

ROLINE GOLD DisplayPort Cable, DP-DP, M/M, 2.0 m

Product No.	11.04.5645
Manufacturer	ROLINE
Manufacturer No.	11.04.5645
EAN (single piece)	7611990194773

roline
Designed for Professionals



2560p

4K

ROLINE DisplayPort Cable with DP connection on both sides for connecting an Ultrabook, Notebook/Laptop or PC to a monitor, TV or projector - for screen transmissions in excellent quality with resolutions of up to 3840x2160 / 4096x2560 @60Hz!

- DisplayPort is a universal connection standard for the transmission of picture and sound signals. Applications include mainly the connection of monitors and televisions to computers, BluRay players and similar devices.
- The connector requires less space and is therefore more suitable for portable display devices (ultrabooks, notebooks/laptops) or for 2 connectors on a graphics card (on a slot plate).
- The practical plug design prevents the cable from slipping out of the DisplayPort socket.
- The robust nylon braid protects the DisplayPort cable effectively and sets it in scene visually.
- High-quality, double-shielded cable (foil+braid) with gold-plated contacts for optimum transmission of image signals
- Gold connector housing

ROLINE GOLD - Top quality without any compromises!

Cables in ROLINE GOLD quality come with high quality shielding and gilded contacts for contact safety even at high plug-in cycles. The plugs are gold coated to enhance their contact durability. Nylon-reinforced outer material in golden/black provides a better stability and gives the cable a stunning look.

- Compliant DP v1.2 (max. 4096 x 2560 @60Hz)

Technical specifications

Manufacturer	ROLINE
Product group	Cable
Product type	DisplayPort Monitor Cable
Colour	black / gold
Length	2 m
Transfer quality	DisplayPort v1.2
Max. resolution	4096 x 2560 @60Hz (4K)
side 1 connector	DisplayPort M
side 2 connector	DisplayPort M
Side 1 Connector Type	DisplayPort
Side 1 Connector Gender	Male
Side 2 Connector Type	DisplayPort
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Screened