

5 pieces 4 In. 8 TPI Special for Aluminum T-Shank Jig Saw Blades **T127D**

- Versatile blade for aluminum 3/16 In. to 5/8 In. thick, fiberglass 3/16 In. to 3/4 In. thick, and plastic 3/16 In. to 1-1/4 In. thick
- 8 TPI tooth design for fast, straight cuts
- HSS construction for long life
- Proper lubricant is recommended when cutting metal
- 4 In. overall length, 3 In. working length
- 5 piece pack



Specifications: T127D 5 pieces 4 In. 8 TPI Special for Aluminum T-Shank Jig Saw Blades

Type	Special for Aluminum
Teeth Per Inch	8
Overall Length	4"
Type of Cut	Fast, straight cuts
Quantity	5
Application	Aluminum 3/16" - 5/8", fiberglass 3/16" - 3/4", plastic 3/16" - 1-1/4"
Tooth Design	Side set and milled
Material	High Speed Steel
Working Length	3"
Blade Thickness	0.04"
Blade Height	0.3"
*Note	If cutting metal, use cutting oil to cool blade. Use only with GCFI-protected outlets or adapters