

LED PIPE


LED PIPE L1200 NW

0051369



Product features

- LED T5 replacement batten, seamless linking (up to 10M), ideal for direct lighting such as under cabinet or in kitchens, 120 degree beam angle, includes switch, includes 0.30m stripped cable, white polycarbonate body, includes standard and tilting brackets



PRODUCT OVERVIEW

Product name	LED PIPE L1200 NW
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
General application	Residential & Consumer, Retail
ETIM Class	EC000109
E-number FI	4278214
Warranty	3 years
Fixture luminous flux (lm)	1275
Luminaire efficacy (lm/W)	111
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Beam Angle (°)	120
Photobiological Risk Group	RG0
Total power consumption (W)	11.5
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Housing colour	White
IP rating	IP20
IK rating	IK03
Product EAN number	5410288513690

DATA TABLE

General data

Product name	LED PIPE L1200 NW
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
General application	Residential & Consumer, Retail
Operating temperature range (°C)	-20°C...+40°C

LED PIPE

LED PIPE L1200 NW

0051369

Performance ambient temperature Tq (°C)	25
ETIM Class	EC000109
E-number FI	4278214
Warranty	3 years

Optical data

Fixture luminous flux (lm)	1275
Luminaire efficacy (lm/W)	111
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Beam Angle (°)	120
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	11.5
Mains voltage (V)	220-240V
Lamp power factor	0.7
Electrical protection	Class II
Control gear required	No
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Drive current (mA)	100
Inrush Current (A)	100
Inrush Duration (µs)	150
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	D
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	111
Max. Luminaires per 13A C Breaker	144
Max. Luminaires per 16A C Breaker	181
Max. Luminaires per 20A C Breaker	222
Max. Luminaires per 10A B Breaker	65
Max. Luminaires per 13A B Breaker	86
Max. Luminaires per 16A B Breaker	107
Max. Luminaires per 20A B Breaker	133

Lifetime data

Lifespan L70 B50	30000
------------------	-------

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK03
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1200
Nominal Product Width (mm)	24

LED PIPE

LED PIPE L1200 NW
0051369

Nominal Product Height (mm)	35
Weight (kg)	0.17


Packaging

Single packaging type	Carton
Product EAN number	5410288513690
Packaging single length / height (cm)	120.4
Packaging single width (cm)	4.6
Packaging single depth (cm)	3.1
DUN14 (outer)	15410288513697
Units per outer package	24
Packaging outer length / height (cm)	122.0
Packaging outer width (cm)	20.5
Packaging outer depth (cm)	21.5

Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------

PHOTOMETRY



TECHNICAL DRAWINGS

