

## SVJC clamp holder with internal cooling, positive

For copy, longitudinal face lathing with VC indexable insert

**ATORN**<sup>®</sup>

### Application

For copy, longitudinal and face turning with VC indexable insert, 35°

### Version

- precision-made steel carrier with high-performance cooling system, nickel-plated, hardened, type V, attack angle 93°, tip angle 35°, clearance angle 7°

### Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable working
- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces
- Very good surface quality for medium infeed and finishing



<b>Art. no.</b>	<b>17833 730</b>
<b>ISO name</b>	SVJC R/L 2525 M16 IK G1/8
<b>Shaft height</b>	25 mm
<b>Shank width</b>	25 mm
<b>Length</b>	150 mm
<b>Length of head</b>	32.5 mm
<b>Programming size</b>	32 mm
<b>Suitable for indexable inserts</b>	VC.. 1604..
<b>Tool design</b>	Right
<b>DIN</b>	4983

### EAN-Code

4050293566697