

Micrometer

Robust, light metal bracket

Hartig

Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

Execution:

- Scale with anti-glare, brushed chromium plated finish
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force
- Robust, light metal bracket
- Measuring spindle hardened and ground from one piece
- Bolted hand-warmth insulation plates

Advantage:

- Measuring spindle increment: 1 mm (direct 1/100 reading for prevention of reading errors, no need to add the 0.5 mm value)

Delivery:

In high-quality wooden case



| | |
|---|------------------|
| Art. no. | 31345 110 |
| Brand | HARTIG |
| Manufacturer Part Number | 1168 250-275 H |
| Min./max. length measuring range | 250-275 mm |
| Vernier scale | 0.01 mm |
| Measuring surface diameter | 8 mm |
| Measuring spindle increments | 1 mm |
| Spindle clamping | No |
| Display | Nonius |
| DIN | 863 |
| Calibration Group | D |
| Gross Weight | 2.100 kg |
| Product Group | 316 |