


Fuse plug - PV-PRO/OE-200/F-1000/14 - 1214613

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Photovoltaic connector, Range of articles: SUNCLIX, Fuse plug, color: black, min. conductor cross section: 6 mm², max. conductor cross section: 6 mm², nom. voltage: 1000 V DC (bis 4000m ü. NN), rated current: 14 A, Connection method: open cable end, min. cable diameter: 5.80 mm, max. cable diameter: 6.40 mm. SUNCLIX fuse element for protecting panels and devices in photovoltaic systems

Key Commercial Data

| | |
|--------------------------------------|--|
| Packing unit | 8 pc |
| Minimum order quantity | 8 pc |
| GTIN |  4 063151 293581 |
| GTIN | 4063151293581 |
| Weight per Piece (excluding packing) | 22.220 g |
| Country of origin | Poland |
| Sales Key | ABLBEA |

Technical data

Ambient conditions

| | |
|---------------------------------|--|
| Ambient temperature (operation) | -40 °C ... 55 °C (Depending on the current carrying capacity/derating curve) |
| Ambient temperature (assembly) | -25 °C ... 50 °C |

General

| | |
|------------------------------|--|
| Standards/regulations | 2PFG 2380-2014-02 in progress |
| Rated surge voltage | 12 kV |
| Degree of pollution | 2 |
| Degree of protection | IP66 / IP68 (2 m / 24 h) |
| Rated voltage | 1000 V |
| Fuse-link nominal current | 15 A DC (Nominal current of the fuse-link) |
| Fuse adapter nominal current | 14 A DC (Nominal current of the item) |
| Protection class | II |

Material

| | |
|-------|-------|
| Color | black |
|-------|-------|

Connection data

| | |
|-------------------|----------------|
| Connection method | open cable end |
|-------------------|----------------|

Fuse plug - PV-PRO/OE-200/F-1000/14 - 1214613

Technical data

Standards and Regulations

| | |
|--|-------------------------------|
| Standards/specifications | 2PFG 2380-2014-02 in progress |
| Flammability rating according to UL 94 | V0 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 9.0 | 27440107 |
|------------|----------|