

ESD shelf trolley with 3 load areas

Load area sizes 850 x 500 and 1000 x 600 mm

Application:

For transporting non-stacking goods and materials, for continuous use in industrial applications. Electrically conductive design.

Version:

- Welded steel tube and profile steel, bolted construction
- Shelves made of electrically conductive wooden plate in accordance with DIN 68765, light grey.
- 1 fixed shelf

Advantage:

- Reliable dissipation of electric charges thanks to continuously conductive structure
- Robust design and high load capacity ensure a long service life even when used for high industrial loads
- Multiple load areas provide ample storage space for non-stacking goods and crates
- FETRA plug-and-screw design allows trolleys and accessories to be modified easily
- Large high-quality castors for good running properties



Art. no.	50268 721
Load-carrying capacity	600 kg
Load-carrying capacity of loading surfaces	50 kg
Colour	Slate grey RAL 7015
Material of loading surface	Wood, electroconductive
Number of loading surfaces	4
Loading surface size	1000 x 600 mm
Loading surface length	1000 mm
Loading-surface width	600 mm
Length	1169 mm
Width	609 mm
Height	1152 mm
Length x width x height	1169 x 609 x 1152 mm
Surface	Powder-coated
Loading-surface height	276 mm
Loading-surface height 2	676 mm
Loading-surface height 3	1076 mm
Made in	Germany
EN standard	1757-3
With wheel lock	Yes
Wheel diameter	200 mm
Material of wheel	TPE-ESD
Wheel width	40 mm
Total stop optional	Yes
Number of fixed rollers	2
Number of steering rollers	2

EAN-Code

4017976091013