

Stereo microscope modular system - Heads KERN OZB-M



Head of the microscope series OSF-5 (OSF 512, 516)



Head of the microscope series OZL-46 (OZL 461, 462)



Head of the microscope series OZM-5 (OZM 546, 547)



Head of the microscope series OZP-5 (OZP 551, 552)



Head of the microscope series OZO-5 (OZO 556, 557)

Individuality, variety and flexible working through our modular construction system ► Stereo microscope heads

Features

- To enable the highest level of flexibility for your special requirements and applications, we have a large selection of stereo microscope heads, universal stands and external illumination units, which are easy to combine
- Through the different properties of the stereo microscope heads, as well as the flexibility of the universal stands and the professional fixing of our brackets, we can configure your ideal microscope to suit your needs
- There are various microscope heads available from our product range for this purpose, both as binocular or trinocular versions
- A C-mount adapter is required to connect a camera to the trinocular version. You can select this adapter from the corresponding model outfit lists on the following pages

Technical data

- Optical system: Greenough optics
- Further technical data and model features is located in the tables below on the following pages
- OSF-5: p. 76
- OZL-46: p. 76
- OZM-5: p. 77
- OZP-5: p. 78
- OZO-5: p. 79

Model	Tube	Tube angle	Eyepieces (included)	Interpupilary distance	Objective	Magnification ratio	Diopter adjustment
KERN					Zoom		
OSF 512*	Binocular	45°	HSWF 10×/Ø 23 mm	52-76 mm	1×/2×	-	One-sided (-6/6)
OSF 516*	Binocular	45°	HSWF 10×/Ø 23 mm	52-76 mm	2×/4×	-	One-sided (-6/6)
OZL 461	Binocular	45°	HWF 10×/Ø 20 mm	55-75 mm	0,7×-4,5×	6,4:1	Both-sided (-5/5)
OZL 462	Trinocular	45°	HWF 10×/Ø 20 mm	52-76 mm	0,7×-4,5×	6,4:1	Both-sided (-5/5)
OZM 546	Binocular	45°	HSWF 10×/Ø 23 mm	52-76 mm	0,7×-4,5×	6,4:1	Both-sided (-6/6)
OZM 547	Trinocular	45°	HSWF 10×/Ø 23 mm	52-76 mm	0,7×-4,5×	6,4:1	Both-sided (-6/6)
OZP 551	Binocular	35°	HSWF 10×/Ø 23 mm	52-76 mm	0,6×-5,5×	9,2:1	Both-sided (-6/6)
OZP 552	Trinocular	35°	HSWF 10×/Ø 23 mm	52-76 mm	0,6×-5,5×	9,2:1	Both-sided (-6/6)
OZO 556*	Binocular	35°	HSWF 10×/Ø 23 mm	52-76 mm	0,8×-7×	8,8:1	Both-sided (-6/6)

MICROSCOPES & REFRACTOMETERS 2023

KERN PICTOGRAMS





360° rotatable microscope head



Monocular Microscope For the inspection with one eye



Binocular Microscope For the inspection with both eyes



Trinocular Microscope

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination

For pictures bright and rich in contrast



LED illumination

Cold, energy-saving and especially long-life illumination



Incident illumination

For non-transparent objects



Transmitting illumination

For transparent objects



Fluorescence illumination

For stereomicroscopes



Fluorescence illumination for compound microscopes

With 100 W mercury lamp and filter



Fluorescence illumination **for compound microscopes**With 3 W LED illumination and filter



Phase contrast unit

For a higher contrast



Darkfield condenser/unit

For a higher contrast due to indirect illumination



Polarising unit

To polarise the light

00

Infinity system

Infinity corrected optical system



Zoom magnification

For stereomicroscopes



Auto-focus

For automatic control of the focus level



Parallel optical system

For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD card

For data storage



USB 2.0 digital camera

For direct transmitting of the picture to a PC



USB 3.0 digital camera

For direct transmitting of the picture to a PC



WIFI data interface:

For transmitting of the picture to a mobile display device



HDMI digital camera

For direct transmitting of the picture to a display device



PC software

To transfer the measurements from the device to a PC.



Automatic temperature compesation

For measurements between 10 °C and 30 °C



Protection against dust and water

splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013

ABBREVIATIONS

C-Mount Adapter for the connection of a camera to a trinocular microscope

FPS Frames per second

High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses) H(S)WF

LWD Long Working Distance N.A. **Numerical Aperture** SLR camera Single-Lens Reflex camera

SWF Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)

W.D. Working Distance

WF Wide Field (Field number up to Ø 22 mm for 10× eyepiece) Battery operation rechargeable Prepared for a rechargeable battery



■→)

RECHARGE

BATT

operation

Battery operation

Plug-in power supply 230V/50Hz in standard version for EU. On request GB, AUS or USA version.

Ready for battery operation. The battery

type is specified for each device.



Integrated power supply unit

Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.