

# High-performance drill SC TiAlNplus HPC 12xD with internal cooling HA

for universal use up to 1300 N/mm<sup>2</sup>



## Application

for HPC boring up to a strength of 1300 N/mm<sup>2</sup>

## Version

- solid carbide TiAlNplus high-performance drill
- 4 drill heels
- Four grinding faces
- 30° spiral angle
- Straight main cutting edge

## Advantage

- economic drilling in a wide variety of materials with high cutting values
- newly developed geometry in conjunction with a multi-layer coating individually tailored to drilling ensures significantly longer service lives
- Cutting edge finishing reduces micro-fractures and increases the service life
- very high alignment accuracy thanks to 4 drill heels
- high process reliability even at extreme depths

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	135	110	90	35	30	210	260	230	180	160	130	60		110	40	35	30		

<b>Art. No.</b>	<b>11110 083</b>
<b>Cutting edge diameter</b>	8.3 mm
<b>Tolerance of cutting edge diameter</b>	h7
<b>Cutting material</b>	VHM
<b>Surface</b>	TiAlN plus
<b>Max. drilling depth (D)</b>	12xD
<b>Type</b>	HPC UNI
<b>Coolant supply</b>	Internal
<b>Tool holding device</b>	HA parallel shank
<b>Angle of the tip</b>	135 Degree
<b>Shaft diameter</b>	10 mm
<b>Chip flute length</b>	120 mm
<b>Length</b>	162 mm
<b>f steel 1000</b>	0.15 mm/r

## EAN-Code

4050293531879