


64572 1000 W 230 V

Halogen studio lamps, double-ended



Areas of application

- Professional film and TV work
- Theater and concert stages
- Entertainment

Product family features

- Operation at mains voltage: 120 V | 230 V | 240 V
- Color temperature: 3,200 K (for professional film and TV work)
- Color temperature: 3,400 K (for maximum luminous efficacy)



Product datasheet

Technical data

Product information

Order reference	64572
-----------------	-------


Electrical data

Nominal wattage	1000.00 W
Nominal voltage	230 V
On-mode power	1045.00 W
Energy consumption in on-mode	1045.0 kWh/1000h

Photometrical data

Color temperature	3200 K
Color rendering index Ra	100
Φ_{use} value refers to luminous flux ..	360
Correlated color temperature CCT	3131 K
Useful luminous flux (Φ_{use})	24030 lm
Chromaticity coordinate x	0.428
Chromaticity coordinate y	0.401

Dimensions & weight



Diameter	18.0 mm
Length	88.4 mm
Length with base excl. base pins/connection	88.40 mm

Lifespan

Lifespan	150 h
----------	-------

Additional product data

Product datasheet

Base (standard designation)	R7s
Lighting technology used	HL

Capabilities

Burning position	Any
------------------	-----

Certificates & standards

Energy efficiency class	G
-------------------------	---

Country specific categorizations

ANSI code	Other
LIF	P2/35
Order reference	64572

Logistical data

EAN 10 of contained light source	4008321325181
----------------------------------	---------------

Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	05-03-2024
Primary Article Identifier	4008321325181
Candidate List Substance 1	No declarable substances contained
Declaration No. in SCIP database	No declarable substances contained

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4008321325181	OSRH64572	-	-	-
4008321325181	OSRH64572	-	-	-

Product datasheet

Safety advice

To prevent personal injury or damage to property, halogen lamps may only be operated in suitable luminaires designed with suitable mechanisms (protective shields, grids, etc.) to ensure that in the event of a lamp bursting no parts/shards can escape and that during operation no ultraviolet radiation can escape. There must also be a warning sign to indicate that the lamps give off high levels of heat. Detailed information is available on request.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321325181	64572 1000 W 230 V	Folding carton box 1	33 mm x 33 mm x 112 mm	0.12 dm ³	17.00 g
4008321325198	64572 1000 W 230 V	Shipping carton box 50	345 mm x 180 mm x 127 mm	7.89 dm ³	1046.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

A summary of studio lamps can be found on the halogen studio lamps poster.
For more information on halogen lamps for studio, stage and TV see the brochure:
"Good news for show business"
"Halogen High Voltage Lamps" cross reference list

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.
