

**Industrial Ethernet
IE-ANT-P-ABG-75-9-NF**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

- For usage with the Weidmüller WLAN Access Point
- Omni-directional and planar antennas
- For use in the 2.4 GHz and 5 GHz band
- Open-air use possible thanks to the robust design (up to IP68)
- Cable for connecting external antennas to the Weidmüller WLAN Access Point in 2-metre and 4-metre versions

General ordering data

Type	IE-ANT-P-ABG-75-9-NF
Order No.	1367140000
Version	Directional antenna, Dual Band (2.4 GHz / 5 GHz), Gain of 6 dBi, Vertical, 1x N-type female, bottom, IP67, Impedance: 50 Ω
GTIN (EAN)	4050118186338
Qty.	1 pc(s).

**Industrial Ethernet
IE-ANT-P-ABG-75-9-NF**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	80 mm	Width (inches)	3.15 inch
Height	101 mm	Height (inches)	3.976 inch
Depth	35 mm	Depth (inches)	1.378 inch
Weight	110 g	Net weight	120 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Enclosure material

Colour	grey	Housing main material	PC
--------	------	-----------------------	----

Included in delivery

Included in delivery 1 x antenna, 1 x wall mounting

Technical data

3dB beamwidth (horizontal)	Band 1: 75°, Band 2: 55°	3dB beamwidth (vertical)	Band 1: 55°, Band 2: 55°
Antenna gain	Band 1: 9 dBi, Band 2: 9 dBi	Composite power max.	10 W
Frequency range	Band 1: 2400 - 2500 (MHz), Band 2: 5150 - 5875 (MHz)	Impedance	50 Ω
Polarisation	Vertical	Radiation	Directional
Standing wave ratio	< 2	Type of connection	1x N-type female, bottom
Vertical electrical tilt	Band 1: 0°, Band 2: 0°	front-to-back ratio	Band 1: 15 dB, Band 2: 15 dB

Environmental conditions

Applications	for indoor and outdoor use	Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	80 °C
Storage temperature, min.	-40 °C	Wind load	Frontal, Lateral, 7 N, @ 160 Km/h

Classifications

ETIM 6.0	EC001698	eClass 6.2	27-25-92-90
eClass 7.1	27-25-92-90	eClass 8.1	19-17-01-90
eClass 9.0	19-07-01-05	eClass 9.1	19-07-01-05

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue [CAT 9 IETH 15/16 EN](#)

Creation date May 27, 2019 3:49:04 PM CEST