


Product description	M12-A female angled connector, Contacts: 8, shielded, moulded cable, IP67, UL, PVC grey, 8 x 0.25 mm ² , 10 m
Area	M12-A series 763
Part no.	77 3534 0000 20708-1000

Illustration



Scale drawing



Contact arrangement (Plug-in side)



- 1 white
- 2 brown
- 3 green
- 4 yellow
- 5 grey
- 6 pink
- 7 blue
- 8 red

Shielded versions: shield = housing

Technical data

General features

Part no.	77 3534 0000 20708-1000
Connector design	female angled connector
Cable length	10 m
Version	female angled
Connector locking system	screw
Termination	moulded cable
Degree of protection	IP67
Cross-sectional area	0.25 mm ² / AWG 24
Temperature range from/to	-25 °C / 90 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	166.00
Customs tariff number	85444290

Electrical parameters

Rated voltage	60 V
Rated voltage UL	2457
Rated impulse voltage	800 V
Rated current (40 °C)	2,0 A
Insulation resistance	≥ 10 ¹⁰ Ω
Pollution degree	3
Overvoltage category	II
Insulating material group	II
EMC compliance	shielded
Shield connection	Shield on the threaded ring

Product description	M12-A female angled connector, Contacts: 8, shielded, moulded cable, IP67, UL, PVC grey, 8 x 0.25 mm ² , 10 m
Area	M12-A series 763
Part no.	77 3534 0000 20708-1000

Material

Housing material	PUR
Contact body material	PUR
Contact material	CuSn (bronze)
Contact plating	Au (gold)
Locking material	CuZn (brass)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	89f8a2ce-13d9-45dd-a4c2-b76a8319496e

Authorization/approvals

Approvals	UL
-----------	----

Classifications

eCl@ss 11.1	27-06-03-11
ETIM 7.0	EC001855

Declarations of conformity

RoHS Directive	2011/65/EU (EN 50581:2012)
----------------	----------------------------

Cable data - Structure of the cable

Cable diameter	6.8 mm
Cross section	8 x 0.25 mm ²
Sheath material	PVC
Single-lead insulation	PVC
Single-lead structure	32 x 0.10 mm
Cable color	grey

Cable data - Electrical properties

Conductor resistance	75 Ω/Km (20°C)
----------------------	----------------

Cable data - Mechanical properties

Bending radius, fixed cable	≥ 5 x Ø
Bending radius, moving cable	≥ 10 x Ø
Bending cycles	>2 million
Permitted acceleration	max. 5 m/s ² + 1 m/s ²
Travel distance, horizontal	5 m/s ² -> 5 m
Travel distance, vertical	5 m/s ² -> 2 m
Travel speed	≤ 200 m/min (5 m horizontal distance)

Product description	M12-A female angled connector, Contacts: 8, shielded, moulded cable, IP67, UL, PVC grey, 8 x 0.25 mm², 10 m
Area	M12-A series 763
Part no.	77 3534 0000 20708-1000

Cable data - Thermal properties

Temperature range cable in move from/to	-5 °C / 105 °C
Temperature range cable fixed from/to	-40 °C / 105 °C

Cable data - Other features

Halogen free	No
--------------	----

Product description	M12-A female angled connector, Contacts: 8, shielded, moulded cable, IP67, UL, PVC grey, 8 x 0.25 mm², 10 m
Area	M12-A series 763
Part no.	77 3534 0000 20708-1000

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP 67 and IP 68 are not suitable for use under water. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).