

2755 / 2755B / GH275
GH435 / GH755
GH810 (-6 to -10)

**Nipples without
wire trap**

**Nippel ohne
Ausreiß-
sicherung**



**Nipples sans
gorge pour
nappes**

**Nipples senza
protezione da
strappo**

**Manguitos
roscados sin
seguro de
arranque**

2755(B) / GH275 / GH435 / GH810 (-6 to -10)

GH755





BP

BSP Male 60°, Parallel
Außengewindeanschluss BSP 60°
Mâle BSP cylindrique, cone 60°
Maschio gas, 60°
Macho fijo/BSP 60°

Part Number Skive Steel	Part Number Skive Stainless Steel	Part Number TTC Steel	Part Number TTC Stainless Steel	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
41.020-6-6*		1T6BP6**		G 3/8"			10	-6	55,0	25,5		6,5		19	
41.020-8-8*		1T8BP8**		G 1/2"			12	-8	61,0	28,0		9,0		22	
41.020-10-10*		1T10BP10**		G 5/8"			16	-10	68,0	27,4		12,0		27	
41.020-12-12*		1T12BP12**		G 3/4"			19	-12	71,0	33,5		15,0		32	
41.020-16-16*		1T16BP16**		G 1"			25	-16	77,0	36,5		20,0		36	

2755(B) / GH275 / GH435 / GH810 (-6 to -10)

GH755



BT

BSP Male Tapered, BSPT
Außengewindeanschluss, BSPT (Stutzen)
Mâle BSP conique
Maschio BSPT (maschio gas conico)
Macho fijo BSPT

Part Number Skive Steel	Part Number Skive Stainless Steel	Part Number TTC Steel	Part Number TTC Stainless Steel	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
41.493-6-6*		1T6BT6**		R 3/8"			10	-6	57,5	28,0		6,5		19	
41.493-8-8*		1T8BT8**		R 1/2"			12	-8	66,5	33,5		9,0		22	
41.493-12-12*		1T12BT12**		R 3/4"			19	-12	76,5	39,0		15,0		32	
41.493-16-16*		1T16BT16**		R 1"			25	-16	82,3	41,8		20,0		36	

* Sockets must be ordered separately.

* Fassungen müssen separat bestellt werden.

* Les jupes doivent être commandées sêp.

* Le boccole devono essere ordinate sep.

* Los manguitos tienen que pedirse por separado.

** Part numbers include sockets.

** Teil-Nr. beinhaltet Fassung.

** L'embout-Nr. avec la jupe.

** Part Number include la boccola.

** Los números de parte incluyen los manguitos.