

BS 6004 624-Y Twin and Earth PVC Cable



Application:

Domestic wiring cable. Can be installed in fixed installations in dry or damp premises clipped to surface, on trays or in free air where the risk of mechanical damage would not be an issue. Suitable for laying in conduit or trunking where mechanical protection is required.

Construction:

Conductor

Copper conductor according to BS EN 60228 (previously BS 6360)

1mm² to 2.5mm²: Class 1 solid conductor 4mm² to 16mm²: Class 2 stranded conductor

Insulation

PVC (Polyvinyl Chloride) Type TI1 according to BS EN 50363

Sheath

PVC (Polyvinyl Chloride) Type 6 according to BS 7655

Cable Standards:

BS 6004 Table 4









The electrical and dimensional properties of this product are measured by the Technical and Quality Assurance department at the Eland Cables laboratory. Cable performance in respect of conductor resistance, construction quality (workmanship). dimensional consistency, and other parameters are verified to published standards and approved product drawings. Conformance to RoHS (Restriction of the use of Hazardous Substances) is determined and confirmed.

Characteristics:

Voltage Rating (Uo/U) 300/500V

Temperature Rating

-5°C to +70°C

Short Circuit: +160°C

Minimum Bending Radius

Fixed:6 x overall diameter

Core Identification

Brown Blue



Sheath Colour



Grey



BS 6004 624-Y

Twin and Earth PVC Cable

Dimensions:

| Order code | Part No. | No. of cores | Nominal cross sectional area mm | Conductor class | Cross sectional area of circuit protective conductor mm ² | Nominal thickness of insulation mm | Nominal thickness of sheath mm | Nominal overall diameter HxW mm | Nominal weight kg/km |
|---------------|-----------|--------------|---------------------------------------|--------------------|--|---|---|--|----------------------------|
| 02-0252 | UTE2010GR | 2 | 1 | 1 | 1 | 0.6 | 0.9 | 4.35 x 7.95 | 68 |
| 02-0253 | UTE2015GR | 2 | 1.5 | 1 | 1 | 0.7 | 0.9 | 4.85 x 8.9 | 87 |
| 02-0254 | UTE2025GR | 2 | 2.5 | 1 | 1.5 | 0.8 | 1 | 5.65 x 10.65 | 120 |
| 02-0255 | UTE2040GR | 2 | 4 | 2 | 1.5 | 0.8 | 1 | 6.3 x 11.95 | 172 |
| 02-0256 | UTE2060GR | 2 | 6 | 2 | 2.5 | 0.8 | 1.1 | 7.1 x 13.7 | 235 |
| 02-0257 | UTE210GR | 2 | 10 | 2 | 4* | 1 | 1.2 | 8.7 x 17.25 | 373 |

^{*}Class 2 conductors only

Conductors:

Class 1 Solid Conductors for Single Core and Multi-Core Cables

| Name in all and a second and a second | Maximum resistance of conductor at 20°C | | |
|--|---|--|--|
| Nominal cross sectional area mm ² | Plain Wires ohms/km | | |
| 1 | 18.1 | | |
| 1.5 | 12.1 | | |
| 2.5 | 7.41 | | |

The above table is in accordance with BS EN 60228 (previously BS 6360)

Class 2 Stranded Conductors for Single Core and Multi-Core Cables

| | Minimum no. of wires in conductor | Maximum resistance of conductor at 20°C | |
|------------------------------|-----------------------------------|---|--|
| Nominal cross sectional area | | Annealed Copper Conductor | |
| mm ² | Circular | Plain Wires ohms/km | |
| 4 | 7 | 4.61 | |
| 6 | 7 | 3.8 | |
| 10 | 7 | 1.83 | |

The above table is in accordance with BS EN 60228 (previously BS 6360) $\,$



BS 6004 624-Y **Twin and Earth PVC Cable**

Electrical characteristics:

Current Carrying Capacity and Voltage Drop

| Nominal cross sectional area mm² | Reference method A* (in conduit in wall) Amps | Reference method C* (Clipped direct) Amps | Voltage drop mv/A/m |
|----------------------------------|---|---|------------------------|
| 1 | 11.5 | 16 | 44 |
| 1.5 | 14.5 | 20 | 29 |
| 2.5 | 20 | 27 | 18 |
| 4 | 26 | 37 | 11 |
| 6 | 32 | 47 | 7.3 |
| 10 | 44 | 64 | 4.4 |

The above table is in accordance with 4D5 of the 17th Edition of IEE Wiring Regulations.

A* For full installation method refer to Table 4A2 Installation Method 2 but for flat twin and earth cable of the 17th Edition of IEE Wiring Regulations.

C* For full installation method refer to Table 4A2 Installation Method 20 but for flat twin and earth cable of the 17th Edition of IEE Wiring Regulations.