

SVGC clamp holder, positive, right

for copy, longitudinal face lathing with VC indexable insert

ATORN[®]

Application

for copy, longitudinal and face turning with VC indexable insert, 35°

Version

- precision-manufactured steel support, bronzed, hardened, type V, working angle 90°, tip angle 35°, clearance angle 7°

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces
- excellent surface quality for medium infeed and finishing
- Very good surface quality for medium infeed and finishing



Art. no.	17836 250
ISO name	SVGC R/L 0808 K07
Shaft height	8 mm
Shank width	8 mm
Length	125 mm
Length of head	15 mm
Programming size	8.5 mm
Suitable for indexable inserts	VC.. 0702..
Tool design	Right

EAN-Code

4050293543933