

# EMG-650P - Electret Gooseneck Microphone



**Electret gooseneck microphone**, with switchable low cut filter.

This microphone features an excellent radiation and a clear voice reproduction.

- Cardioid polar pattern
- Wide transmission range
- Switchable low cut 180 Hz (12 dB/oct)
- Electronically balanced output
- Low acoustic feedback
- Unobtrusive power LED in the XLR connection terminal
- Foam windshield
- Total length: 600 mm

## Technical Data

Type	: gooseneck microphone
Version	: -
Transmission method	: cable
Polar pattern	: cardioid
System	: electret
Carrier frequency range	: -
Transmitting power	: -
Power supply	: -
Operating time	: -
Audio frequency range	: 30-18,000 Hz
Nominal impedance	: 180 Ohm
Sensitivity	: 4.5 mV/Pa
S/N ratio	: -
Maximum sound pressure	: 130 dB
Power supply	: DC current 9-48 V, phantom power
Gooseneck length	: -
Material (housing/cabinet)	: -
Admiss. ambient temp.	: 0-40 °C
Dimensions	: Ø 9/19 mm x 600 mm
Weight	: 175 g
Cable	: -
Connection	: XLR