



OPTIONS



VERSIONS

Type	Current per Winding A	Holding Torque Ncm	Resistance per Winding Ohm	Inductance per Winding mH	Rotor Inertia gcm ²	Weight kg	Length „A“ mm
ST6018X2008	1.41	106.07	1.46	2.2	275	0.6	47
ST6018X3008	2.12	110.31	0.68	0.8	275	0.6	47
ST6018M2008	1.41	195.16	2	4.6	400	0.77	56
ST6018M3008	2.12	165.46	0.8	1.38	400	0.77	56
ST6018K2008	1.41	212.13	2.4	4.6	570	1.2	67
ST6018L3008	2.12	353.55	1.3	3.2	840	1.45	88
ST6018D4508	3.18	400.22	0.75	1.4	1100	1.9	111

The current and holding torque values refer to bipolar serial wiring. The resistance and inductance values refer to unipolar wiring.


ORDER IDENTIFIER







ST6018X2008-

- A = single shaft
- B = double shaft




DIMENSIONS (IN MM)



TORQUE CURVES



TORQUE CURVES



Notes section with horizontal lines for writing.