

Micrometer

Interchangeable anvil

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

Advantage:

- With interchangeable measuring anvil for a variable measuring range

Delivery:

Includes box, setting standard, measuring inserts, adjustment wrench



Art. no.	32016 154
Brand	MITUTOYO
Manufacturer Part Number	104-146A
Min./max. length measuring range	700-800 mm
Vernier scale	0.01 mm
Measuring surface diameter	8 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Display	Nonius
Number of setting dimensions	4 PCS
Number of pieces	8 PCS
Min./max. measurement force	10-14 N
Calibration Group	D
Gross Weight	14.500 kg
Product Group	3MA

EAN

4946368215181