

Lever gauge

MarTest



Application:

For measuring deviations in concentricity, axial run-out, parallelism and flatness. For centring shafts, boreholes and aligning workpieces.

Execution:

- Impact-resistant movement
- Dial sealed with O-ring
- Anti-magnetic components
- Automatic switching of callipers direction
- Measuring element supported in 8 precious stones
- 3 dovetail mounting surfaces

Advantage:

- Viewing window made of mineral glass, therefore resistant to solvents



| | |
|---|------------------|
| Art. no. | 33303 080 |
| Brand | MAHR |
| Manufacturer Part Number | 4306250 |
| Length measuring range | 0.5 mm |
| Scale value | 0.01 mm |
| Measurement force | 0.07 N |
| Length of measuring sensor from centre of ball | 41.3 mm |
| Material of measuring ball | Carbide |
| Ball diameter | 2 mm |
| Pivot range of measuring sensor | 220 Degree |
| Diameter | 38 mm |
| Connection thread | M2 |
| DIN | 2270 |
| Calibration Group | L |
| Gross Weight | 0.160 kg |
| Product Group | 305 |

EAN

4059192013530