

Flexible 3-sided machining. You can machine up to 4 workpieces at once. Art. No. 1586.410

Units	Designation	Art. No.
1	Clamping bar	1585.300
1	Fixing screws	1585.301
3	Stop, flat, two-sided	1586.070
2	Taper clamping unit, M8 clamping jaw flat, two-sided	23250.0502




Two ranges of 1586.410. Particularly well suited for machining long workpieces. Art. No. 1586.411

Units	Designation	Art. No.
2	Clamping bar	1585.300
2	Fixing screws	1585.301
6	Stop, flat, two-sided	1586.070
4	Taper clamping unit, M8 clamping jaw flat, two-sided	23250.0502



Units	Designation	Art. No.
1	Clamping bar	1585.300
1	Fixing screws	1585.301
2	Stop, flat, two-sided	1586.070
1	Taper clamping unit, M12 clamping jaw flat, two-sided	23250.0511



Flexible 3-sided machining. 1-2 workpieces can be machined at the same time.

Art. No. 1586.412

Flexible 3-sided machining. Particularly well suited for machining long workpieces. Art. No. 1586.413


Units	Designation	Art. No.
2	Clamping bar	1585.300
2	Fixing screws	1585.301
6	Stop, flat, two-sided	1586.070
4	Taper clamping unit, M12 clamping jaw flat, two-sided	23250.0511

STANDARD RANGES



For machining large workpieces. Art. No. 1586.414

Units	Designation	Art. No.
2	Clamping bar	1585.100
2	Fixing screws	1585.101
2	Clamping bar	1585.200
2	Fixing screws	1585.201
4	Stop, flat, two-sided	1586.070
2	Taper clamping unit, M8 clamping jaw flat, two-sided	23250.0511



For machining cylindrical workpieces. 4 workpieces can be machined at the same time. Art. No. 1586.415

Units	Designation	Art. No.
1	Clamping bar	1585.400
1	Fixing screws	1585.401
1	Stop, V-blocks vertical, two-sided	1586.040
2	Stop, 1-sided, V-blocks vertical and flat	1586.041
2	Taper clamping unit, M8 clamping jaw flat, two-sided	23250.0502



For machining large workpieces. Including supports with a height of 15 mm. Art. No. 1586.416

Units	Designation	Art. No.
2	Clamping bar	1585.300
2	Fixing screws	1585.301
4	Stop, flat, two-sided	1586.070
4	Support for clamping bar	1586.200
2	Taper clamping unit, M12 clamping jaw flat, two-sided	23250.0511