

Part no.: 50106961
MTKS 14x23.P
Reflector



Figure can vary

Contents

- Technical data
- Dimensioned drawings

Part no.: 50106961 – MTKS 14x23.P – Reflector

Technical data

Basic data	
Area of application	Pharmaceutical
Mechanical data	
Design	Rectangular
Mounting dimension, width	13.6 mm
Reflection surface width	11 mm
Mounting dimension, height	23 mm
Reflection surface height	21 mm
Mounting dimension, thickness	4.2 mm
Triple reflector size	1.2 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PES
Structure, active surface	Mikrotriple
Net weight	2 g
Type of fastening	Adhesive Through-hole mounting
Compatibility of materials	ECOLAB
Environmental data	
Ambient temperature, operation	-40 ... 65 °C
Certifications	
Degree of protection	IP 67
Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

