

shrink-fit extensions with IC
with straight shank

ATORN®

Application

For extending and reducing to smaller diameters.

Version

- With 4.5 ° angle
- Clamping diameter for shaft tolerance h 6
- Workpiece stop screw with 10 mm adjustment travel



Art. No.	23431 614
Clamping diameter	5 mm
Outer diameter	20 mm
Tapered diameter	10 mm
Length	150 mm

EAN-Code

4050293418095