

Pneumatic countersink drill bit BS 502

MANNESMANN
DEMAG

Execution:

- Cold insulated, ergonomic handle
- With self-start by contact pressure
- With speed control

Advantage:

- Extremely quiet and robust
- Easy handling, especially for large workpieces
- Low air consumption, as drive is only applied during the work process



Art. no.	75061 265
Brand	MANNESMANN DEMAG
Manufacturer Part Number	29602465
Model	BS 502
Valve design	Thrust start
Max. idle speed	500 rpm
Air consumption	5.6 l/s
Max. clamping diameter	8 mm
Min./max. idle speed	0-500 rpm
Suitable for bore diameter	30 mm
Length	230 mm
Diameter of housing	31 mm
Weight	0.65 kg
Spot-facer diameter	30 mm
Max. bore diameter	30 mm
Connection thread	G 1/4 inch
Power output	160 W
With speed control	Yes
Sound-pressure level	65 dB
Gross Weight	1.459 kg
Product Group	7AA

EAN

4251757300134