


KEL - SNAP

SNAP frames



Type	Order No.	Fits for	Cut-out [mm]	PU	Description
KEL - SNAP B4	42038	KEL-B KEL-Quick B	46 x 38	10	
KEL - SNAP 10	42039	KEL 10	46 x 65	10	
KEL - SNAP 16	42040	KEL 16 KEL-Quick 16	46 x 85	10	
KEL - SNAP 24	42042	KEL 24 KEL-FG A KEL-Quick 24	46 x 112	10	
KEL - SNAP 24E	42044	KEL 24-E	71 x 112	1	
KEL - SNAP 24MT	42046	KEL 24-MT	89 x 112	1	

Product description

The KEL-SNAP frame provides quick assembly of the KEL system when necessary. Control panels already in the factory can be equipped with the KEL-SNAP frame allowing a simple push in of the KEL frame once the associated equipment is delivered to the factory.

A cut-out of 46 mm also can be chosen instead of 36mm. Thus pre-fabricated multi pole connectors can be used.

Advantages

- Upon disassembly (e.g. maintenance) screwing and unscrewing of KEL-frame is not necessary
- Previously assembled KEL frames are quickly and easily attached
- Integrated gasket in SNAP-frame
- Drilling template identical to KEL-frame (except KEL-SNAP B4)

Specification

Material	Polyamide
Flame class	UL-94 Vo, self-extinguishing
Protection class	IP 54
Temperature	- 40°C to + 140°C (static)
Properties	halogen-free, silicone-free
Drilling template	see page 120 121

Accessories

KEL Cable entry frames	Page 6 15
KEL-QUICK Cable entries	Page 36
MP Module plates	Page 108
BPM-SNAP Blind plates	Page 112