



TAOGLAS®



Datasheet

Taoglas Reach Series - PCS.86.A

Description:

Reach - Low Profile Wideband Cellular - 5G/4G SMD Antenna

Features:

- Patent Pending Innovative Design
- High Efficiency Wideband Antenna, Covering 791 to 6000 MHz
- 5G NR Frequency Band 1 Support
- Backwards Compatible with all 3G/2G applications
- Surface Mount Distribution - Supplied on Tape & Reel
- Dimensions: 32 x 16 x 1.6 mm
- RoHS & REACH Compliant

1.	Introduction	3
2.	Specifications	5
3.	Antenna Characteristics	6
4.	2D Radiation Patterns	9
5.	3D Radiation Patterns	12
6.	Mechanical Drawing	17
7.	Layout Dimensions	18
8.	EVB Dimensions	19
9.	Matching Circuit	20
10	Packaging	21
	Changelog	22

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.



1. Introduction



The Taoglas Reach series, are a revolutionary, low profile, small footprint, range of patent pending SMD mount PCB wide-band antennas. The PCS.86.A has been designed to cover 4G cellular bands and all sub-6 GHz 5G deployments across the 791MHz to 6000MHz spectrum on a very small footprint of just 32 x 16mm. It also covers 3G and 2G bands to allow for fall-back when 5G/4G is not available.

The patent pending design uses printed circuit board material and innovative design techniques to deliver the highest efficiencies at all bands when mounted on the device's main PCB. The PCS.66.A is suitable for lower cost 4G applications, especially IoT projects requiring wide bandwidth and comes supplied on tape and reel to allow it be mounted via 'pick & place' onto the PCB.

If tuning is required, it can also be tuned specifically depending on device environment. If the extended 5G/4G Band 71 is required, the Reach PCS.66, covering 600 – 6000MHz, could be an option with a slightly larger footprint of 32 x 25mm. Contact your regional Taoglas customer support team for advice on integrating the Reach into your device.

1.1 Key Advantages

1. **Highest efficiency in small footprint** A comparative antenna to the Reach, for example, metal/ceramic/FPC, would have much-reduced efficiency in this configuration due to their high substrate loss at high frequencies. Very high efficiency antennas are critical to 4G and 5G devices ability to deliver the stated data-speed rates of systems such as 5G NR and LTE.
2. **Low profile** Many antennas require a large keep-out area in addition to the mechanical size to work correctly, which limits the usable PCB space. The Reach requires only .3 mm of additional keep-out, allowing board designers to maximize their PCB space.
3. **Adaptable** The high radiation efficiency of the Reach over its entire operating bandwidth means that the total efficiency is only limited by the impedance mismatch loss. As a result, this antenna can be optimized via a matching network to the specific bands needed for any application. Efficiencies as high as 90% have been measured when the return loss is very high (-15 dB or more).
4. **More resistant to detuning compared to other antenna integrations.** If tuning is required it can be tuned for the device environment using a matching circuit, or other techniques on the main PCB itself. There is no need for new tooling, thereby saving money if customization is required.
5. **Surface Mount Distribution (SMD)** Direct mount, 'on-board' antennas save on labor, cable and connector costs, leads to higher integration yield rates and reduces losses in transmission.
6. **Minimum Transmission and Reception Losses** These are kept to an absolute minimum resulting in much improved OTA (over the air), i.e. TRP (Total Radiated Power) / TIS (Total Isotropic Radiation), device performance compared to similar efficiency cable and connector antenna solutions. This means it is an ideal antenna to be used for devices that need to pass for example USA carrier network approvals.

2. Specifications

Electrical								
Standard	LTE/GSM/ CDMA	5G NR Band 74,75,76	LTE/GSM/ HSPA/ CDMA	UMTS/ HSPA	Wi-Fi 2400	LTE 2600	5G NR Band 77,78,79	Wi-Fi 5800
Operation Frequency (MHz)	791-960	1427-1518	1710-1990	1920-2170	2400-2500	2500-2700	3300-5000	5150-5850
Peak Gain	1.5 dBi	1.2 dBi	4.6 dBi	3.5 dBi	5.1 dBi	4.6 dBi	4.9 dBi	.728 dBi
Average Gain	-2.3 dB	-3.7 dB	-1.6 dB	-1.9 dB	-2.2 dB	-1.9 dB	-2 dB	-4.4 dB
Efficiency	60%	43%	69%	64%	60%	64%	63%	36%
VSWR	<3.0:1							
Impedance	50Ω							
Polarization	Linear							
Radiation Properties	Omni-directional							
Max Input Power	5 W							


The Reach PCS.86.A antenna performance was measured on a 107x32 ground plane

Mechanical	
Dimensions	32mm x 16mm x 1.6mm
Material	PCB
Termination	Solder Pad
EVB Connector	SMA-Female

Environmental	
Operation Temperature	-40°C to 85°C
Storage Temperature	-40°C to 105°C
Relative Humidity	Non-condensing 65°C 95% RH
RoHs Compliant	Yes


3. Antenna Characteristics

3.1 Test Setup




On PCSD.86.A Evaluation Board


3.2 Return Loss




3.3 VSWR




3.4 Efficiency



3.5 Peak Gain








3.6 Average Gain








4. 2D Radiation Patterns (Measured on 123*32mm EVB)






XY Plane



YZ Plane




XZ Plane




5. 3D Radiation Patterns

5.1 123*32mm EVB


790MHz




875MHz




960 MHz




1425 MHz




1520 MHz




1710 MHz




1850 MHz




1910 MHz




2450 MHz




2550 MHz




2700 MHz




3300 MHz




4300 MHz




6000 MHz



6. Mechanical Drawing (Units: mm)




7. Layout Dimensions




Please note that the center of mass is 1.16mm offset in the positive Y dimension from the geometric X-Y center of the antenna.

8. EVB Drawing




9. Matching Circuit




Circuit Symbol	Size	Description
L1	0402	7.5nH inductor (L-07C7N5JV6T)
C1	0402	3pF Capacitor (GJM1555C1H3R0BB01D)

10. Packaging


800pcs PCS.86.A per Tape & Reel
 Dimensions - $\varnothing 330 \times 56$ mm
 Weight – 2.2Kg




800pcs PCS.86.A per Box
 Dimensions - 350*340*85mm
 Weight – 2.3Kg



2400pcs PCS.86.A per Carton
 Dimensions - 360*370*305mm
 Weight – 7Kg



Pallet Dimensions:
 1100*720*1270mm
 24 Cartons Per Pallet
 6 Cartons Per Layer
 4 Layers



Changelog for the datasheet

SPE-19-8-013 – PCS.86.A

Revision: C (Current Version)

Date:	2020-01-10
Changes:	Updated drawings
Changes Made by:	Jack Conroy

Previous Revisions

Revision: B

Date:	2019-04-26
Changes:	Added Packaging
Changes Made by:	Jack Conroy

Revision: A (Original First Release)

Date:	2019-02-22
Notes:	Initial Datasheet Release
Author:	Yu Kai Yeung



TAOGLAS®

www.taoglas.com

