

MINITWS LED Light Module



RND 430-00094 (24V)
RND 430-00098 (240V)

RND 430-00093 (24V)
RND 430-00097 (240V)

RND 430-00095 (24V)
RND 430-00099 (240V)

RND 430-00096 (24V)
RND 430-00100 (240V)

Modulo luminoso a led.

*Led luminous module.
Module lumineux à LED
LED-Lichtmodul
Módulo de luz LED*

CUPOLA <i>DOME DOME HAUBE CÚPULA</i>	PC						
GHIERA <i>RING BAGUE RING CONTERA</i>	PC						
GRUPPO OTTICO <i>LUMINOUS SOURCE SOURCE LUMINEUSE LICHTQUELLE FUENTE DE LUZ</i>	N°4 LED						
COLORI DISPONIBILI <i>AVAILABLE COLOURS COULEURS DISPONIBLES VERFÜGBARE FARBEN COLORES DISPONIBLES</i>							
TENSIONE DI ALIMENTAZIONE <i>VOLTAGE TENSION SPANNUNG TENSIÓN</i>	24 Vdc/Vac – 240Vac						
SERVIZIO <i>OPERATION FONCTIONNEMENT BETRIEBSART FUNCIONAMIENTO</i>	∞						
CORRENTE NOMINALE <i>CURRENT CONSUMPTION CONSUMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE</i>	<table border="1"> <thead> <tr> <th></th> <th>24 Vac/dc</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <th>mA</th> <td>30</td> <td>55</td> </tr> </tbody> </table>		24 Vac/dc	240Vac	mA	30	55
	24 Vac/dc	240Vac					
mA	30	55					
RESA LUMINOSA <i>LIGHT OUTPUT RENDEMENT LUMINEUX LICHT LEISTUNG SALIDA DE LUZ</i>							
MODALITA' LUCE <i>LIGHT EFFECT EFFET LUMINEUX LICHTEFFEKT EFECTO LUMINOSO</i>	Fissa - Lampeggiante <i>Steady - Flashing Fixe - Clignotante Dauerlicht - Blinklicht Luz fija - Luz intermitente</i>						
GRADO IP <i>IP RATING DEGRE IP SCHUTZART GRADO IP</i>	IP66						

MINITWS LED Light Module



TEMPERATURA DI FUNZIONAMENTO <i>OPERATING TEMPERATURE TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR TEMPERATURA DE FUNCIONAMIENTO</i>	-30°C+50°C
VIBRAZIONI <i>VIBRATIONS VIBRATIONS VIBRATIONEN VIBRACIONES</i>	INDUSTRIAL CEI 60068-2-6 SINE
CERTIFICAZIONI, OMOLOGAZIONI <i>CERTIFICATIONS, APPROVALS CERTIFICACIONES, HOMOLOGATIONS PRODUKTZERTIFIKATE, ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES</i>	CE, UKCA
FISSAGGIO <i>MOUNTING FIXATION FIXIERUNG FIJACIÓN</i>	Tramite ghiera <i>Ring Bague Ring Contera</i>
DISEGNO <i>TECHNICAL DRAWING DESSIN TECHNISCHE ZEICHNUNG DIBUJO TECNICO</i>	<p>The technical drawing shows a side view of the LED light module. It is a cylindrical component with a mounting ring at the bottom. Dimension lines indicate a total height of 50 units, an inner diameter of 48 units, and an outer diameter of 55 units.</p>