

MATERIAL

C10 zinc-plated steel.

RIVETS

Zinc-plated steel.

PULLING PIN AND HOOK

Zinc-plated steel.

HANDLE

Polyurethane, red colour.

STANDARD EXECUTIONS


- **MTA-T**: with pulling pin.
- **MTA-TF**: with pulling hook.

FEATURES AND APPLICATIONS


All articulated joints are lubricated with special grease.

MTA. clamps ensure tight closing of any cover.


The position of the pulling hook (MTA-TF) can be adjusted according to specific applications.



MTA-T



MTA-TF



MTA-T

| Code | Description | a | b1 | b2 | b3 | d1 | d3 | h1 | h2 | l1 | l2 | m1 | m2 | s | Stroke w | FH [N]* | △ |
|----------|-------------|----|----|----|----|----|------|------|----|-----|------|------|------|---|----------|---------|------|
| GG.AL200 | MTA.200-T | 37 | 35 | 45 | 18 | 10 | 6.5 | 49 | 16 | 203 | 43 | 32 | 19 | 3 | 100 | 2000 | 300 |
| GG.AL300 | MTA.300-T | 35 | 48 | 60 | 21 | 10 | 8.3 | 49 | 18 | 226 | 43 | 45 | 32 | 3 | 104 | 3000 | 460 |
| GG.AL400 | MTA.400-T | 43 | 54 | 84 | 26 | 14 | 10.5 | 60.5 | 25 | 278 | 45.5 | 60.5 | 28.5 | 5 | 160 | 4000 | 1000 |

MTA-TF

| Code | Description | a | b1 | b2 | d2 | d3 | h1 | h2 | l1 | l2 | m1 | m2 | r | s | Stroke w | FH [N]* | △ |
|----------|-------------|----|----|----|----|------|------|----|-----|---------|------|------|---|---|----------|---------|------|
| GG.AL205 | MTA.200-TF | 29 | 35 | 45 | 8 | 6.5 | 49 | 16 | 250 | 85+105 | 32 | 19 | 5 | 3 | 100 | 2000 | 380 |
| GG.AL305 | MTA.300-TF | 25 | 48 | 60 | 10 | 8.5 | 49 | 18 | 305 | 90+120 | 45 | 32 | 6 | 3 | 104 | 3000 | 560 |
| GG.AL405 | MTA.400-TF | 30 | 54 | 84 | 11 | 10.5 | 60.5 | 25 | 343 | 105+135 | 60.5 | 28.5 | 7 | 5 | 160 | 4000 | 1200 |

* Holding force.

