

Hydraulic hand pumps

For single-acting cylinders



Application:

For operating hydraulic cylinders.

Execution:

- The piston hand pumps comprise a pump unit, drain valve and oil reservoir.
- The pumps can be used with the pump head downwards both horizontally and vertically.
- Ready for operation with oil filling
- Single-acting cylinder.

Advantage:

- Automatic switch-over from low pressure to high pressure range in two-stage pumps.

Delivery:

1x ENERPAC hydraulic hand pump P 18.



Art. no.	29701 080
Brand	ENERPAC
Manufacturer Part Number	P462
Model	P-462
Number of steps	2
Max. operating pressure 1. Level	14 bar
Max. operating pressure 2. Level	700 bar
Feed volume per stroke	121.2 cm ³
Feed volume per stroke 2	4.75 cm ³
Usable oil volume	7428 cm ³
Connection thread	NPTF 3/8 inch - 18
Weight	27 kg
Gross Weight	0.340 kg
Product Group	258