

Deburring machine for contours – Speedy contour



Application:

The stationary edge and contour milling machines are perfect for machining square and round workpieces with flush internal and external contours. They are compact and convenient table-top devices, which are ideal for use with CNC machines.

Execution:

- Chamfer angle can be changed using contour milling cutters with different tip angles
- Suitable for continuous operation
- Suitable for machining small to medium-sized workpieces
- Speed control (only for Speedy Kontur 270-KSL and Speedy Kontur 320-KSL)
- Can be used for steels, hardened steels, aluminium, brass, copper, plastics, from soft plastics to acrylic glass, wood and much more
- Guide ball bearing min. dia. 3 mm

Advantage:

- For precise deburring and chamfering of inner and outer edges on flat workpieces
- Ideal for machining aluminium and plastic
- Fast set-up with maximum flexibility
- Simple operation, fast tool change



Art. no.	79304 300
Brand	ASSFALG
Manufacturer Part Number	1011
Type	Speedy Kontur 270-K
Max. chamfer width	2 mm
Motor speed	22000 rpm
Motor output	0.14 kW
Nominal voltage	230 V
Length x width x height	270 x 170 x 120 mm
Weight	8 kg
Gross Weight	8.000 kg
Product Group	788