



SIMATIC S7-400H, CPU 417-5H, CENTRAL UNIT FOR S7-400H AND S7-400F/FH, 5 INTERFACES: 1X MPI/DP, 1X DP, 1X PN AND 2 FOR SYNC MODULES 32 MB MEMORY (16 MB DATA/16 MB CODE)

Product type designation	
General information	
Hardware product version	1
Firmware version	V6.0
Engineering with	
<ul style="list-style-type: none"> Programming package 	As of STEP 7 V5.5 SP2 with HF1
CiR - Configuration in RUN	
CiR synchronization time, basic load	60 ms
CiR synchronization time, time per I/O byte	0 µs
Supply voltage	
Rated value (DC)	
<ul style="list-style-type: none"> 24 V DC 	No; Power supply via system power supply
Input current	
from backplane bus 5 V DC, typ.	1.6 A
from backplane bus 5 V DC, max.	1.9 A
from backplane bus 24 V DC, max.	150 mA; 150 mA per DP interface
from interface 5 V DC, max.	90 mA; At each DP interface
Power losses	
Power loss, typ.	7.5 W
Memory	
Type of memory	other
Work memory	
<ul style="list-style-type: none"> Integrated 	32 Mbyte

• integrated (for program)	16 Mbyte
• integrated (for data)	16 Mbyte
• expandable	No
Load memory	
• expandable FEPRAM	Yes; with Memory Card (FLASH)
• expandable FEPRAM, max.	64 Mbyte
• integrated RAM, max.	1 Mbyte
• expandable RAM	Yes
• expandable RAM, max.	64 Mbyte
Backup	
• present	Yes
• with battery	Yes; all data
• without battery	No
Battery	
Backup battery	
• Backup current, typ.	180 µA; Valid up to 40°C
• Backup current, max.	1 000 µA
• Backup time, max.	Dealt with in the module data manual with the secondary conditions and the factors of influence
• Feeding of external backup voltage to CPU	5 to 15 VDC
CPU processing times	
for bit operations, typ.	7.5 ns
for word operations, typ.	7.5 ns
for fixed point arithmetic, typ.	7.5 ns
for floating point arithmetic, typ.	15 ns
CPU-blocks	
DB	
• Number, max.	16 000; Number range: 1 to 16000
• Size, max.	64 kbyte
FB	
• Number, max.	8 000; Number range: 0 to 7999
• Size, max.	64 kbyte
FC	
• Number, max.	8 000; Number range: 0 to 7999
• Size, max.	64 kbyte
OB	
• Number, max.	see instruction list
• Size, max.	64 kbyte
• Number of free cycle OBs	1; OB 1
• Number of time alarm OBs	8; OB 10-17
• Number of delay alarm OBs	4; OB 20-23

• Number of time interrupt OBs	9; OB 30-38
• Number of process alarm OBs	8; OB 40-47
• Number of DPV1 alarm OBs	3; OB 55-57
• Number of startup OBs	2; OB 100, 102
• Number of asynchronous error OBs	9; OB 80-88
• Number of synchronous error OBs	2; OB 121, 122
Nesting depth	
• per priority class	24
• additional within an error OB	2
Counters, timers and their retentivity	
S7 counter	
• Number	2 048
Retentivity	
— can be set	Yes
— lower limit	0
— upper limit	2 047
— preset	Z 0 to Z 7
Counting range	
— lower limit	0
— upper limit	999
IEC counter	
• present	Yes
• Type	SFB
• Number	Unlimited (limited only by RAM capacity)
S7 times	
• Number	2 048
Retentivity	
— can be set	Yes
— lower limit	0
— upper limit	2 047
— preset	No times retentive
Time range	
— lower limit	10 ms
— upper limit	9 990 s
IEC timer	
• present	Yes
• Type	SFB
• Number	Unlimited (limited only by RAM capacity)
Data areas and their retentivity	
Total retentive data area	Total working and load memory (with backup battery)
Flag	

• Number, max.	16 384 byte
• Retentivity available	Yes
• Retentivity preset	MB 0 to MB 15
• Number of clock memories	8; in 1 memory byte
Data blocks	
• Number, max.	16 000; Number range: 1 to 16000
• Size, max.	64 kbyte
Local data	
• adjustable, max.	64 kbyte
• preset	32 kbyte
Address area	
I/O address area	
• Inputs	16 kbyte
• Outputs	16 kbyte
of which, distributed	
— MPI/DP interface, inputs	2 kbyte
— MPI/DP interface, outputs	2 kbyte
— DP interface, inputs	8 kbyte
— DP interface, outputs	8 kbyte
— PN interface, inputs	8 kbyte
— PN interface, outputs	8 kbyte
Process image	
• Inputs, adjustable	16 kbyte
• Outputs, adjustable	16 kbyte
• Inputs, default	1 024 byte
• Outputs, default	1 024 byte
• consistent data, max.	244 byte
• Access to consistent data in process image	Yes
Subprocess images	
• Number of subprocess images, max.	15
Digital channels	
• Inputs	131 072
— Inputs, of which central	131 072
• Outputs	131 072
— Outputs, of which central	131 072
Analog channels	
• Inputs	8 192
— Inputs, of which central	8 192
• Outputs	8 192
— Outputs, of which central	8 192
Hardware configuration	

Expansion devices, max.	21
connectable OPs	119
Multicomputing	No
Interface modules	
• Number of connectable IMs (total), max.	6
• Number of connectable IM 460s, max.	6
• Number of connectable IM 463s, max.	4; Single mode only
Number of DP masters	
• Integrated	2
• Via CP	10; CP 443-5 Extended
• Mixed mode IM + CP permitted	No
• via interface module	0
Number of IO Controllers	
• Integrated	1
• Via CP	0
Number of operable FMs and CPs (recommended)	
• FM	See manual Automation System S7-400H fault-tolerant systems. Limited by number of slots and number of connections
• CP, point-to-point	See manual Automation System S7-400H fault-tolerant systems. Limited by number of slots and number of connections
• PROFIBUS and Ethernet CPs	14; Of which max. 10 CP as DP master
Slots	
• Required slots	2
Time of day	
Clock	
• Hardware clock (real-time clock)	Yes
• battery-backed and synchronizable	Yes
• Resolution	1 ms
• Deviation per day (buffered), max.	1.7 s; Power off
• Deviation per day (unbuffered) max.	8.6 s; Power on
Operating hours counter	
• Number	16
• Number/Number range	0 to 15
• Range of values	SFCs 2, 3 and 4: 0 to 32767 hours SFC 101: 0 to 2 ³¹ - 1 hours
• Granularity	1 hour
• retentive	Yes
Clock synchronization	
• supported	Yes
• to MPI, master	Yes
• to MPI, slave	Yes
• to DP, master	Yes
• to DP, slave	Yes

• in AS, master	Yes
• in AS, slave	Yes
• on Ethernet via NTP	Yes; As client
Time difference in system when synchronizing via	
• Ethernet, max.	10 ms; Via NTP
• MPI, max.	200 ms
Interfaces	
Number of RS 485 interfaces	2
Number of other interfaces	2; Fiber-optic interface
1st interface	
Interface type	Integrated
Physics	RS 485 / PROFIBUS + MPI
Isolated	Yes
Power supply to interface (15 to 30 V DC), max.	150 mA
Number of connection resources	MPI: 44, DP: 32
Functionality	
• MPI	Yes
• DP master	Yes
• DP slave	No
MPI	
• Number of connections	44; If a diagnostics repeater is used on the line, the number of connection resources on the line is reduced by 1
• Transmission rate, max.	12 Mbit/s
Services	
— PG/OP communication	Yes
— Routing	Yes
— Global data communication	No
— S7 basic communication	No
— S7 communication	Yes
— S7 communication, as client	Yes
— S7 communication, as server	Yes
DP master	
• Number of connections, max.	32; If a diagnostics repeater is used on the line, the number of connection resources on the line is reduced by 1
• Transmission rate, max.	12 Mbit/s
• Number of DP slaves, max.	32
Services	
— PG/OP communication	Yes
— Routing	Yes
— Global data communication	No
— S7 basic communication	No

— S7 communication	Yes
— S7 communication, as client	Yes
— S7 communication, as server	Yes
— Equidistance mode support	No
— Isochronous mode	No
— SYNC/FREEZE	No
— Activation/deactivation of DP slaves	No
— Direct data exchange (slave-to-slave communication)	No
— DPV1	Yes
Address area	
— Inputs, max.	2 kbyte
— Outputs, max.	2 kbyte
User data per DP slave	
— User data per DP slave, max.	244 byte
— Inputs, max.	244 byte
— Outputs, max.	244 byte
— Slots, max.	244
— per slot, max.	128 byte
DP slave	
• Number of connections	No configuration of CPU as DP slave
2nd interface	
Interface type	PROFINET
Physics	Ethernet RJ45
Isolated	Yes
Integrated switch	Yes
Number of ports	2
Automatic detection of transmission speed	Yes; Autosensing
Autonegotiation	Yes
Autocrossing	Yes
Change of IP address at runtime, supported	No
Number of connection resources	120
Media redundancy	
• supported	Yes
• Switchover time on line break, typically	200 ms
• Number of stations in the ring, max.	50
Functionality	
• DP master	No
• DP slave	No
• PROFINET IO Controller	Yes
• PROFINET IO Device	No
• PROFINET CBA	No

• Open IE communication	Yes
• Web server	No
• Point-to-point connection	No
PROFINET IO Controller	
• Transmission rate, max.	100 Mbit/s
• Number of connectable IO devices, max.	256; In redundant mode via both interfaces
• Max. number of connectable IO devices for RT	256
— of which in line, max.	256
• Shared device	Yes; Single mode only
• Prioritized startup	No
• Activation/deactivation of IO Devices	No
• IO Devices changing during operation (partner ports), supported	No
• Device replacement without swap medium	Yes
• Send cycles	250 μ s, 500 μ s, 1 ms, 2 ms, 4 ms
• Updating time	250 μ s to 512 ms, minimum value depends on the number of configured user data and the configured single or redundant mode
Services	
— PG/OP communication	Yes
— S7 routing	Yes
— S7 communication	Yes
— Isochronous mode	No
— Open IE communication	Yes
Address area	
— Inputs, max.	8 kbyte
— Outputs, max.	8 kbyte
— User data consistency, max.	1 024 byte
Open IE communication	
• Number of connections, max.	118
• Local port numbers used at the system end	0, 20, 21, 25, 102, 135, 161, 34962, 34963, 34964, 65532, 65533, 65534, 65535
• Keep-alive function, supported	Yes
3rd interface	
Interface type	Integrated
Physics	RS 485 / PROFIBUS
Power supply to interface (15 to 30 V DC), max.	150 mA
Number of connection resources	32
Functionality	
• DP master	Yes
• DP slave	No
DP master	
• Number of connections, max.	32

• Transmission rate, min.	9.6 kbit/s
• Transmission rate, max.	12 Mbit/s
• Number of DP slaves, max.	125
Services	
— PG/OP communication	Yes
— Routing	Yes
— Global data communication	No
— S7 basic communication	No
— S7 communication	Yes
— S7 communication, as client	Yes
— S7 communication, as server	Yes
— Equidistance mode support	No
— Isochronous mode	No
— SYNC/FREEZE	No
— Activation/deactivation of DP slaves	No
— Direct data exchange (slave-to-slave communication)	No
— DPV0	Yes
— DPV1	Yes
Address area	
— Inputs, max.	8 kbyte
— Outputs, max.	8 kbyte
User data per DP slave	
— User data per DP slave, max.	244 byte
— Inputs, max.	244 byte
— Outputs, max.	244 byte
— Slots, max.	244
— per slot, max.	128 byte
4th interface	
Interface type	Pluggable synchronization submodule (FO)
Plug-in interface modules	Synchronization modules 6ES7960-1AA06-0XA0 or 6ES7960-1AB06-0XA0
5. Interface	
Interface type	Pluggable synchronization submodule (FO)
Plug-in interface modules	Synchronization modules 6ES7960-1AA06-0XA0 or 6ES7960-1AB06-0XA0
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	No
equidistance	No
Communication functions	

PG/OP communication	Yes
<ul style="list-style-type: none"> • Number of connectable OPs without message processing • Number of connectable OPs with message processing 	119 119; When using Alarm_S/SQ and Alarm_D/DQ
Data record routing	Yes
S7 routing	Yes
Global data communication	
<ul style="list-style-type: none"> • supported 	No
S7 basic communication	
<ul style="list-style-type: none"> • supported 	No
S7 communication	
<ul style="list-style-type: none"> • supported • as server • As client • User data per job, max. • User data per job (of which consistent), max. 	Yes Yes Yes 64 kbyte 462 byte; 1 variable
S5-compatible communication	
<ul style="list-style-type: none"> • supported • User data per job, max. • User data per job (of which consistent), max. • Number of simultaneous AG-SEND/AG-RECV orders per CPU, max. 	Yes; (via CP max. 10 and FC AG_SEND and FC AG_RECV) 8 kbyte 240 byte 64/64
Standard communication (FMS)	
<ul style="list-style-type: none"> • supported 	Yes; Via CP and loadable FB
Open IE communication	
<ul style="list-style-type: none"> • TCP/IP <ul style="list-style-type: none"> — Number of connections, max. — Data length, max. — Several passive connections per port, supported • ISO-on-TCP (RFC1006) <ul style="list-style-type: none"> — Number of connections, max. — Data length, max. • UDP <ul style="list-style-type: none"> — Number of connections, max. — Data length, max. 	Yes; via integrated PROFINET interface and loadable FBs 118 32 kbyte Yes Yes; Via integrated PROFINET interface or CP 443-1 and loadable FBs 118 32 kbyte; 1452 bytes via CP 443-1 Adv. Yes; via integrated PROFINET interface and loadable FBs 118 1 472 byte
Web server	
<ul style="list-style-type: none"> • supported 	No
Number of connections	
<ul style="list-style-type: none"> • overall • usable for PG communication 	120

- reserved for PG communication
- Adjustable for PG communication, max.
- usable for OP communication
 - reserved for OP communication
 - adjustable for OP communication, max.
- usable for S7 basic communication
 - Reserved for S7 basic communication
 - adjustable for S7 basic communication, max.
- usable for S7 communication
 - reserved for S7 communication
 - Adjustable for S7 communication, max.
- usable for routing
 - Reserved for routing
 - adjustable for routing, max.

1
0
1
0
0
0
0
0
0
0

S7 message functions

Number of login stations for message functions, max.	119; Max. 119 with Alarm_S/SQ and Alarm_D/DQ (OPs); max. 16 with Alarm_8, Alarm_8P, Notify and Notify_8 (e.g. WinCC)
Symbol-related messages	No
SCAN procedure	No
Block related messages	Yes
Process diagnostic messages	Yes
simultaneously active Alarm-S blocks, max.	1 000; Simultaneously active alarm_S/SQ blocks or alarm_D/DQ blocks
Alarm 8-blocks <ul style="list-style-type: none"> • Number of instances for alarm 8 and S7 communication blocks, max. • preset, max. 	10 000 1 200
Process control messages	Yes
Number of archives that can log on simultaneously (SFB 37 AR_SEND)	64

Test commissioning functions

Status block	Yes
Single step	Yes
Number of breakpoints	16
Status/control <ul style="list-style-type: none"> • Status/control variable • Variables • Number of variables, max. 	Yes; Up to 16 variable tables Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters 70
Forcing <ul style="list-style-type: none"> • Forcing 	Yes

• Force, variables	Inputs/outputs, bit memories, distributed I/Os
• Number of variables, max.	512
Diagnostic buffer	
• present	Yes
• Number of entries, max.	3 200
— can be set	Yes
— preset	120
Service data	
• Can be read out	Yes
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes
• Limit class B, for use in residential areas	No
Configuration	
Configuration software	
• STEP 7	Yes
programming	
• Command set	see instruction list
• Nesting levels	7
• Access to consistent data in process image	Yes
• System functions (SFC)	see instruction list
• System function blocks (SFB)	see instruction list
Programming language	
— LAD	Yes
— FBD	Yes
— STL	Yes
— SCL	Yes
— CFC	Yes
— GRAPH	Yes
— HiGraph®	Yes
Number of simultaneously active SFCs	
— RD_REC	8
— WR_REC	8
— WR_PARM	8
— PARM_MOD	1
— WR_DPARM	2
— DPNRM_DG	8
— RDSYSST	8
— DP_TOPOL	1
Number of simultaneously active SFBs	
— RDREC	8

— WRREC

8

Know-how protection

- User program protection/password protection Yes
- Block encryption Yes; With S7 block Privacy

Dimensions

Width	50 mm
Height	290 mm
Depth	219 mm

Weights

Weight, approx. 995 g

last modified: 12.03.2015