

INSTA TERMINAL, 6MM, 2.5SQMM PE, L, NT, 26A, 400V




Figure similar

General technical data		
Insulation material		thermoplastic
Terminal contact spacing	mm	6
Protection class		
Combustibility class acc. to UL 94		V2
Main circuit		
Operating voltage / Rated value	V	250
Operating current / Rated value	A	24
Appearance		
Color / of the insulating body		black
Product details		
Product feature		
• N function		Yes
• N separation slides		Yes
• PE function		Yes
Product component		
• required / connection plate		No
• Test separator		No
Number		
Number of potentials		3
Connections		
Connectable conductor cross-section / stranded		

• minimum	mm ²	2.5
• maximum	mm ²	2.5
Connectable conductor cross-section		
• solid		
— minimum	mm ²	2.5
— maximum	mm ²	2.5
• finely stranded		
— with core end processing / minimum	mm ²	2.5
— with core end processing / maximum	mm ²	2.5
— without core end processing / minimum	mm ²	2.5
— without core end processing / maximum	mm ²	2.5
Type of electrical connection		
• 1		screw-type terminal
• 2		screw-type terminal
Position / of the terminal		lateral

Mechanical Design		
Height / with lowest-profile installation	mm	42.5
Length	mm	87
Mounting type		DIN rail 35 mm

Environmental conditions		
Ambient temperature		
• during operation / maximum	°C	55

General Product Approval	Test Certificates	other
---------------------------------	--------------------------	--------------



[other](#)

[Environmental Confirmations](#)

[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8WA10113JF20>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8WA10113JF20/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WA10113JF20

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015