



DATA SHEET	0153019
DIN compensating cable KP 13 L-SIL 2x1,5 oval	valid from : 01.12.2008

Application

The compensating cable KP 13 L-SIL 2 x 1,5 mm² is a silicone and glass fibre insulated cable which transmits the thermoelectric voltage of PtRh/Pt thermocouples. It is for fixed installation in dry rooms. It may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range.

Design

Conductor	1,5 mm ² (48 x 0,20 mm)
Conductor material	RCB/SCB alloying, accuracy class 2 according DIN 43722 Positive conductor: Cu (copper) Negative conductor: CuNi (cupronickel)
Core insulation	Silicone compound
Core identification	Positive conductor: red Negative conductor: white
Core layering	Cores parallel next to each other
Outer sheath	Glass fibre braiding with interweaved white identification thread

Electrical properties

Limiting deviation class 2 ± 60 µV (± 5,0 °C) / measuring point temperature +1000 °C

Mechanical and thermal properties

Temperature range	occasional flexing: -25 °C up to +180 °C
Minimum bending radius	occasional flexing: 12 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document: DB0153019EN	page 1 of 1
--	----------------------------	-------------