

# Mains Extensions

## Metal Cable Drum

2 Socket



4 Socket



### Specifications:

Voltage rating : 240 V ac  
Approval category : BS EN61242

### Specification Table

Connector Type A	Connector Type B	Cable Type	Current Rating (A)	Maximum Cross-section Area (mm <sup>2</sup> )	External Diameter	Lead Length (m)	Number of Outputs	Number of Ways	Part Number	
UK Mains Plug	Twin UK Mains	UK Mains	5	1.25	228.6 (9)	15	2	2	2200-2-15M	
						25			2200-2-25M	
	Four UK Mains		13		15	304.8 (12)	20	4	4	2200-4-15M
					25		2200-4-20M			
			-		25	2200-4-25M				
			-		30	2200-4-30M				
			-		40	2250-4-40M				
			-		50	2250-4-50M				

Dimensions : Millimetres (Inches) (Unless Specified)

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro - ELEC is the registered trademark of the Group. © Premier Farnell plc 2011.