


DEBUR AND BREAK SHARP EDGES


DO NOT SCALE DRAWING

REVISION



PART No.	"A"
TRLCBS-2-10-01	15.9
TRLCBS-2-12-01	19.1
TRLCBS-2-3-01	4.8
TRLCBS-2-4-01	6.4
TRLCBS-2-5-01	7.9
TRLCBS-2-6-01	9.5
TRLCBS-2-7-01	11.1
TRLCBS-2-8-01	12.7

SECTION A-A



SECTION B-B

NOTES

- MATERIAL: PA66 UL94V-2/UL94V0;
- COLOR: NATURAL;
- ROHS Compliant;
- Top Hole: $\varnothing 4.75 \pm 0.08$ mm;
Panel Thickness: 1.98-3.56mm;
- Bottom Hole: $\varnothing 4.0 \pm 0.08$;
Panel Thickness: 1.57mm;



DESIGN RIGHT. TR FASTENINGS LTD, 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED,
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS
SURFACE FINISH:
TOLERANCES:
ISO 2768 m

NAME	DATE
DRAWN MARTIN ELLIOTT	01/11/13
CHK'D	
APP'VD	

CUSTOMER PART No

MATERIAL:
SEE NOTES

HEAT TREATMENT
N/A

FINISH:
N/A

TITLE:
LOCKING CIRCUIT
BOARD SUPPORT

DWG NO.
TRLCBS-2-XX-01

A3