



WSR 208

For WXMPMS MS
Smart Micro / Pico Soldering Iron
Order No. T0051518299

WSR 200

For WXUPS MS
Smart Ultra Soldering Iron
Order No. T0051517499N

WXsmart Soldering Tip Family




WX Smart
2-Channel Power Unit, 300W

WXMPMS MS

Smart Micro/Pico Soldering Iron
40W, 24V
Order No. T0052923699

WXUPS MS

Smart Ultra Soldering Iron
150W, 24V
Order No. T0052923599



RTPS Pico tips

RTMS Micro tips

RTUS Ultra tips

RTPS Smart Pico Tips

- + High performance tips for the smallest components: 0402 down to 01005
- + Short tip-to-grip distance
- + MIL-SPEC / IPC standard (potential free, MS versions)



RTMS Smart Micro Tips

- + High performance active tips for micro and standard components
- + Covers the widest range of geometries and sizes
- + MIL-SPEC / IPC standard (potential free, MS versions)



RTUS Smart Ultra Tips

- + Designed for heavy duty applications and large components
- + Thermal Core Technology for optimized heat transfer
- + MIL-SPEC / IPC standard



Model	Length (mm) (inch.)	a / b (mm) (inch.)	Order No.
CHISEL			
RTPS 002 S MS	16.3 0.642	0.2 / 0.1 0.008 / 0.004	T0050111199
RTPS 002 S NW MS	16.3 0.642	0.2 / 0.1 0.008 / 0.004	T0050111299
RTPS 004 S MS	16.3 0.642	0.4 / 0.2 0.016 / 0.008	T0050111399
RTPS 008 S MS	16.3 0.642	0.8 / 0.3 0.031 / 0.012	T0050111499
RTPS 010 S MS	16.3 0.642	1.0 / 0.3 0.039 / 0.012	T0050111599
RTPS 013 S MS	16.3 0.642	1.3 / 0.3 0.051 / 0.012	T0050111699
BEVEL CUT			
RTPS 004 B MS	16.3 0.642	0.34 0.013	T0050110999
RTPS 012 B MS	16.3 0.642	1.05 0.041	T0050111099
CONICAL			
RTPS 001 C MS	17.9 0.705	0.1 0.004	T0050110399
RTPS 001 CNW MS	17.9 0.705	0.1 0.004	T0050110499
RTPS 002 C MS	16.3 0.642	0.2 0.008	T0050110599
RTPS 004 C MS	16.3 0.642	0.4 0.016	T0050110699
RTPS 001 C X MS	20.6 0.811	0.1 0.004	T0050110799
RTPS 002 C X MS	20.6 0.811	0.2 0.008	T0050110899
GULLWING			
RTPS 020 G MS	15.9 0.626	1.3 / 2.1 0.051 / 0.083	T0050112099
KNIFE			
RTPS 010 K MS	15.9 0.626	1.0 / 0.2 0.039 / 0.008	T0050111799
RTPS 010 KNW MS	15.9 0.626	1.0 / 0.2 0.039 / 0.008	T0050111899
RTPS 025 K MS	17.3 0.681	2.5 / 0.3 0.098 / 0.012	T0050111999

Model	Length (mm) (inch.)	a / b (mm) (inch.)	Order No.
CHISEL			
RTMS 003 S NW MS	19.6 0.772	0.3 / 0.1 0.012 / 0.004	T0050115299
RTMS 004 S MS	19.0 0.748	0.4 / 0.2 0.016 / 0.008	T0050109099
RTMS 006 S MS	23.0 0.906	0.6 / 0.4 0.024 / 0.016	T0050108399
RTMS 008 S MS	23.0 0.906	0.8 / 0.4 0.031 / 0.016	T0050109799
RTMS 008 S X MS	23.0 0.906	0.8 / 0.4 0.031 / 0.016	T0050109499
RTMS 010 S MS	18.0 0.709	1.0 / 0.3 0.039 / 0.012	T0050108499
RTMS 013 S MS	19.0 0.748	1.3 / 0.4 0.051 / 0.016	T0050109199
RTMS 013 S X MS	28.0 1.102	1.3 / 0.5 0.051 / 0.020	T0050108899
RTMS 015 S MS	28.0 1.102	1.5 / 0.5 0.059 / 0.020	T0050109399
RTMS 018 S MS	18.0 0.709	1.8 / 0.4 0.071 / 0.016	T0050108599
RTMS 022 S MS	18.0 0.709	2.2 / 0.4 0.087 / 0.016	T0050109699
BEVEL CUT			
RTMS 004 B MS	18.5 0.728	0.4 0.016	T0050108299
RTMS 012 B MS	18.0 0.709	1.2 0.047	T0050109599
CONICAL			
RTMS 001 C NW MS	19.0 0.748	0.1 0.004	T0050109999
RTMS 002 C MS	19.0 0.748	0.2 0.008	T0050108999
RTMS 002 C L MS	18.7 0.736	0.2 0.008	T0050108199
RTMS 004 C MS	21.4 0.843	0.4 0.016	T0050115399
RTMS 004 C X MS	25.0 1.004	0.4 0.016	T0050110299
RTMS 005 C X MS	26.0 1.024	0.5 0.020	T0050110199
RTMS 008 C MS	18.0 0.709	0.8 0.031	T0050109299
GULLWING			
RTMS 020 G MS	20.0 0.787	2.0 / 1.2 0.079 / 0.047	T0050109899
KNIFE			
RTMS 025 K MS	19.0 0.748	1.8 / 0.3 0.071 / 0.012	T0050108799
RTMS 030 K MS	19.0 0.748	2.2 0.087	T0050115199

Model	Length (mm) (inch.)	a / b (mm) (inch.)	Order No.
CHISEL			
RTUS 015 S MS	28.0 1.102	1.5 / 0.4 0.059 / 0.016	T0050113099
RTUS 022 S MS	28.0 1.102	2.2 / 0.6 0.087 / 0.024	T0050113199
RTUS 032 S MS	27.5 1.083	3.2 / 0.8 0.126 / 0.031	T0050113299
RTUS 032 S L MS	34.0 1.339	3.2 / 0.8 0.126 / 0.031	T0050113399
RTUS 050 S MS	27.5 1.083	5.0 / 1.2 0.197 / 0.047	T0050113499
RTUS 076 S MS	28.0 1.102	7.6 / 1.5 0.299 / 0.059	T0050113599
RTUS 093 S MS	28.0 1.102	9.3 / 2.0 0.366 / 0.079	T0050113699
RTUS 006 S L MS	33.5 1.319	0.6 X 0.3 0.024 x 0.012	T0050114499
RTUS 012 S L MS	32.5 1.280	1.2 X 0.3 0.047 x 0.012	T0050114599
RTUS 018 S L MS	35.0 1.378	1.8 X 0.8 0.071 x 0.031	T0050115099
RTUS 022 S L MS	32.0 1.260	2.2 X 1.0 0.087 x 0.039	T0050114899
BEVEL CUT			
RTUS 020 B MS	29.0 1.142	2.0 0.079	T0050112799
RTUS 035 B MS	29.0 1.142	3.5 0.138	T0050112899
RTUS 050 B MS	32.0 1.260	5.0 0.197	T0050112999
RTUS 015 B L MS	34.0 1.339	1.5 0.059	T0050114799
CONICAL			
RTUS 004 C MS	27.5 1.083	0.4 0.016	T0050112199
RTUS 008 C MS	29.0 1.142	0.8 0.031	T0050112299
RTUS 016 C MS	27.5 1.083	1.6 0.063	T0050112399
RTUS 004 C X MS	39.2 1.543	0.4 0.016	T0050112499
RTUS 008 C X MS	39.2 1.543	0.8 0.031	T0050112599
RTUS 016 C X MS	39.2 1.543	1.6 0.063	T0050112699
RTUS 006 C L MS	33.5 1.319	0.6 0.024	T0050114299
RTUS 003 C L MS	34.0 1.339	0.3 0.012	T0050114399
RTUS 010 C L MS	34.0 1.339	1.0 0.039	T0050114699
GULLWING			
RTUS 020 G MS	28.0 1.102	2.0 / 1.3 0.079 / 0.051	T0050113799
BLADE			
RTUS 100 K MS	27.0 1.063	10.0 / 1.5 0.394 / 0.059	T0050113899
RTUS 160 K MS	27.0 1.063	16.0 / 1.5 0.630 / 0.059	T0050113999
RTUS 200 K MS	27.0 1.063	20.0 / 1.5 0.787 / 0.059	T0050114099
RTUS 330 K MS	27.0 1.063	33.0 / 1.5 1.299 / 0.059	T0050114199
RTUS 060 K L MS	38.0 1.496	4.25 / 0.4 0.167 / 0.016	T0050114999

* from 50 °C to 350 °C / 120 °F to 620 °F

Weller

weller-tools.com/wxsmart

Discover more

