



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 13

LOCTITE EA 3463 known as Loctite 3463

SDS No. : 153766
V008.1

Revision: 04.12.2018
printing date: 10.01.2020

Replaces version from: 24.07.2018

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE EA 3463 known as Loctite 3463

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Epoxy resin

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Skin sensitizer	Category 1
H317 May cause an allergic skin reaction.	
Chronic hazards to the aquatic environment	Category 3
H412 Harmful to aquatic life with long lasting effects.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:**Contains**

reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700)

Signal word:

Warning

Hazard statement:

H315 Causes skin irritation.
 H317 May cause an allergic skin reaction.
 H319 Causes serious eye irritation.
 H412 Harmful to aquatic life with long lasting effects.

Precautionary statement:

***** **For consumer use only: P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P501 Dispose of waste and residues in accordance with local authority requirements***

**Precautionary statement:
Prevention**

P273 Avoid release to the environment.
 P280 Wear protective gloves.

**Precautionary statement:
Response**

P302+P352 IF ON SKIN: Wash with plenty of soap and water.
 P333+P313 If skin irritation or rash occurs: Get medical advice/attention.
 P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures**General chemical description:**

Epoxy resin

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	01-2119456619-26	10- 40 %	Skin Irrit. 2 H315 Skin Sens. 1 H317 Eye Irrit. 2 H319 Aquatic Chronic 2 H411

For full text of the H - statements and other abbreviations see section 16 "Other information".
 Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures**Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:
Rinse with running water and soap.
Obtain medical attention if irritation persists.

Eye contact:
Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:
Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

SKIN: Rash, Urticaria.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well-ventilated areas.

Avoid skin and eye contact.

Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

See advice in section 8

Hygiene measures:

- Wash hands before work breaks and after finishing work.
- Do not eat, drink or smoke while working.
- Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.
Refer to Technical Data Sheet

7.3. Specific end use(s)

Epoxy resin

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for
Great Britain

None

Occupational Exposure Limits

Valid for
Ireland

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (freshwater)		0,006 mg/l				
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (marine water)		0,001 mg/l				
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sewage treatment plant (STP)		10 mg/l				
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sediment (freshwater)				0,996 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sediment (marine water)				0,1 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Soil				0,196 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	oral				11 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (intermittent releases)		0,018 mg/l				

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	dermal	Acute/short term exposure - systemic effects		8,33 mg/kg	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Inhalation	Acute/short term exposure - systemic effects		12,25 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	dermal	Long term exposure - systemic effects		8,33 mg/kg	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Inhalation	Long term exposure - systemic effects		12,25 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	General population	dermal	Acute/short term exposure - systemic effects		3,571 mg/kg	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	General population	dermal	Long term exposure - systemic effects		3,571 mg/kg	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	General population	oral	Acute/short term exposure - systemic effects		0,75 mg/kg	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	General population	oral	Long term exposure - systemic effects		0,75 mg/kg	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	General population	inhalation	Acute/short term exposure - systemic effects		0,75 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	General population	inhalation	Long term exposure - systemic effects		0,75 mg/m3	

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	solid dark grey, up to, black
Odor	pungent
Odour threshold	No data available / Not applicable
pH	Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	> 93,3 °C (> 199.94 °F); Setaflash Closed Cup
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density (ρ)	2,25 g/cm ³
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Insoluble
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Reaction with strong acids.
Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information

11.1. Information on toxicological effects**Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	LD50	> 2.000 mg/kg	rat	OECD Guideline 420 (Acute Oral Toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	LD50	> 2.000 mg/kg	rat	OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	moderately irritating	24 h	rabbit	Draize Test

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 472 (Genetic Toxicology: Escherichia coli, Reverse Mutation Assay)
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	negative	oral: gavage		mouse	not specified

Carcinogenicity

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Sex	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	not carcinogenic	dermal	2 y daily	mouse	male	OECD Guideline 453 (Combined Chronic Toxicity / Carcinogenicity Studies)
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	not carcinogenic	oral: gavage	2 y daily	rat	male/female	OECD Guideline 453 (Combined Chronic Toxicity / Carcinogenicity Studies)

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	NOAEL P >= 50 mg/kg NOAEL F1 >= 750 mg/kg NOAEL F2 >= 750 mg/kg	Two generation study	oral: gavage	rat	OECD Guideline 416 (Two- Generation Reproduction Toxicity Study)

STOT-single exposure:

No data available.

STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	NOAEL 50 mg/kg	oral: gavage	14 w daily	rat	OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents)

Aspiration hazard:

No data available.

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	LC50	1,75 mg/l	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	EC50	1,7 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	NOEC	0,3 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	EC50	> 11 mg/l	72 h	Scenedesmus capricornutum	OECD Guideline 201 (Alga, Growth Inhibition Test)
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	NOEC	4,2 mg/l	72 h	Scenedesmus capricornutum	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	IC50	> 100 mg/l	3 h	activated sludge, industrial	other guideline:

12.2. Persistence and degradability

The product is not biodegradable.

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	not readily biodegradable.	aerobic	5 %	28 d	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)

12.3. Bioaccumulative potential

No data available.

No substance data available.

12.4. Mobility in soil

Cured adhesives are immobile.

Hazardous substances CAS-No.	LogPow	Temperature	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	3,242	25 °C	EU Method A.8 (Partition Coefficient)

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Collection and delivery to recycling enterprise or other registered elimination institution.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information**14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H411 Toxic to aquatic life with long lasting effects.

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.