

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: 175 UNIVERSAL ACRYLIC SEALANT - ALL COLOURS

Product code: 175WE/BN

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: EVERBUILD BUILDING PRODUCTS LTD

SITE 41, KNOWSTHORPE WAY

CROSS GREEN INDUSTRIAL ESTATE

LEEDS

WEST YORKSHIRE

LS9OSW

ENGLAND

Tel: 0044 113 240 3456

Fax: 0044 113 240 0024

Email: sds@everbuild.co.uk

1.4. Emergency telephone number

Emergency tel: 0044 113 240 3456 (office hours only)

Manufacturer: EVERBUILD BUILDING PRODUCTS LTD

Site 41

Knowsthorpe Way, Cross Green Industrial Estate

Leeds

West Yorkshire

LS9 0SW

United Kingdom

Tel: (0044) 113 240 3456

Fax: (0044) 113 240 0024

Emergency tel: (0044) 113 240 3456

Email: sds@everbuild.co.uk

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: This product has no classification under CHIP.

Classification under CLP: This product has no classification under CLP.

SAFETY DATA SHEET

175 UNIVERSAL ACRYLIC SEALANT - ALL COLOURS

Page: 2

2.2. Label elements

Label elements: This product has no label elements.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Wash the spillage site with large amounts of water.

[cont...]

SAFETY DATA SHEET

175 UNIVERSAL ACRYLIC SEALANT - ALL COLOURS

Page: 3

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Store in original containers between +5 and +25°C.
Storage outside these parameters will dramatically reduce shelf life and invalidates all product warranties.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Various

Odour: Barely perceptible odour

Evaporation rate: Slow

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Miscible

Viscosity: Highly viscous

Viscosity test method: x 1000 cps - Brookfield HBDV2+, spindle S70, 10rpm @ 20°C

Boiling point/range°C: 100

Flammability limits %: lower: N/A

upper: N/A

Flash point°C: >93

Autoflammability°C: N/D

Vapour pressure: as water

Relative density: 1.67

pH: 8.5-9.5

VOC g/l: 9.8

[cont...]

SAFETY DATA SHEET

175 UNIVERSAL ACRYLIC SEALANT - ALL COLOURS

Page: 4

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: No data available.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

[cont...]

SAFETY DATA SHEET

175 UNIVERSAL ACRYLIC SEALANT - ALL COLOURS

Page: 5

12.6. Other adverse effects

Other adverse effects: No data available.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Dispose of according to local or national legislation

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Legend to abbreviations: PNEC = predicted no effect level
DNEL = derived no effect level
LD50 = median lethal dose
LC50 = median lethal concentration
EC50 = median effective concentration
IC50 = median inhibitory concentration
dw = dry weight
bw = body weight
cc = closed cup
oc = open cup
MUS = mouse
GPG = guinea pig
RBT = rabbit
HAM = hamster
HMN = human
MAM = mammal
PGN = pigeon

[cont...]

SAFETY DATA SHEET

175 UNIVERSAL ACRYLIC SEALANT - ALL COLOURS

Page: 6

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = physico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.