

Innovative Service Around the Globe

DATA SHEET

SURFACE-MOUNT CERAMIC MULTILAYER CAPACITORS

General purpose & High capacitance

Class 2, Y5V

6.3 ∨ TO 50 ∨ I0 nF to 47 μF RoHS compliant & Halogen Free



YAGEO

2

14

Surface-Mount Ceramic Multilayer Capacitors Y5V SERIES 6.3 V to 50 V

<u>SCOPE</u>

This specification describes Y5V series chip capacitors with lead-free terminations.

APPLICATIONS

Consumer electronics, for

- example:
- Tuners
- Television receivers
- Video recorders
- All types of cameras
- Mobile telephones

FEATURES

Supplied in tape on reel Nickel-barrier end termination RoHS compliant Halogen Free compliant

ORDERING INFORMATION - GLOBAL PART NUMBER, PHYCOMP

CTC & 12NC

All part numbers are identified by the series, size, tolerance, TC material, packing style, voltage, process code, termination and capacitance value.

YAGEO BRAND ordering code

GLOBAL PART NUMBER (PREFERRED)

CC	<u>xxxx</u>	<u>x</u>	<u>X</u>	Y5V	<u>x</u>	BB	<u>xxx</u>
	(1)	(2)	(3)		(4)		(5)

(I) SIZE - INCH BASED (METRIC)

0201	(0603)
0402	(1005)
0603	(1608)
0805	(2012)
1206	(3216)
1210	(3225)

(2) TOLERANCE

 $M = \pm 20\%$

Z = -20% to +80%

(3) PACKING STYLE

R = Paper/PE taping reel; Reel 7 inch

- K = Blister taping reel; Reel 7 inch
- P = Paper/PE taping reel; Reel 13 inch
- F = Blister taping reel; Reel 13 inch

(4) RATED VOLTAGE

5	=	6.3	V
6	=	10	V

- 7 = 16 V
- 8 = 25 V
- 9 = 50 V

(5) CAPACITANCE VALUE

2 significant digits+number of zeros

The 3rd digit signifies the multiplying factor, and letter R is decimal point

Example: $103 = 10 \times 10^3 = 10,000 \text{ pF} = 10 \text{ nF}$



CONSTRUCTION

The capacitor consists of a rectangular block of ceramic dielectric in which a number of interleaved metal electrodes are contained. This structure gives rise to a high capacitance per unit volume.


The inner electrodes are connected to the two end terminations and finally covered with a layer of plated tin (NiSn). The terminations are lead-free. A cross section of the structure is shown in Fig. I.

Table I For outlines see fig. 2



2				L_{2} / L_{3}	, (mm)	L₄ (mm)
TYPE	rPE L _I (mm) W (mm)		T (MM)	min.	max.	min.
0201	0.6 ±0.03	0.3 ±0.03	_	0.10	0.20	0.20
0402	1.0 ±0.05	0.5 ±0.05	_	0.15	0.35	0.30
0603	1.6 ±0.10	0.8 ±0.10	_	0.20	0.60	0.40
0005	2.0 ±0.10 ⁽¹⁾	1.25 ±0.10 ⁽¹⁾		0.25	0.75	0.70
0805	2.0 ±0.20 ⁽²⁾	1.25 ±0.20 ⁽²⁾	_	0.25	0.75	0.70
1207	3.2 ±0.15 ⁽¹⁾	1.6 ±0.15 ⁽¹⁾	Refer to	0.25	0.75	1.40
1206	3.2 ±0.30 ⁽²⁾	1.6 ±0.20 ⁽²⁾	table 2 to 4	0.25	0.75	1.40
1210	3.2 ±0.20 ^()	2.5 ±0.20 ^(I)		0.05	0.75	1.40
1210	3.2 ±0.40 ⁽²⁾	2.5 ±0.30 ⁽²⁾		0.25	0.75	1.40
1012	4.5 ±0.20 ⁽¹⁾	3.2 ±0.20 ^(I)	-	0.05	0.75	2.20
1812	4.5 ±0.40 ⁽²⁾	3.2 ±0.40 ⁽²⁾		0.25	0.75	2.20

OUTLINES



ΝΟΤΕ


I. Dimension for size 0805 to 1812, $C \le 100 \text{ nF}$

2. Dimension for size 0805 to 1812, C > 100 nF

Dec. 21, 2023 V.14

Product specification

 $\frac{3}{14}$



Surface-Mount Ceramic Multilayer Capacitors Y5V SERIES 6.3 V to 50 V

CAPACITANCE RANGE & THICKNESS FOR Y5V

 Table 2
 Sizes from 0201 to 0402

CAP.	0201		0402				
	6.3 V	25 V	6.3 V	10 V	16 V	25 V	50 V
I0 nF	-	0.3±0.03	-	0.5±0.05	0.5±0.05	0.5±0.05	0.5±0.05
22 nF				0.5±0.05	0.5±0.05	0.5±0.05	
47 nF				0.5±0.05	0.5±0.05	0.5±0.05	
100 nF	0.3±0.03		0.5±0.05	0.5±0.05	0.5±0.05	0.5±0.05	
220 nF			0.5±0.05	0.5±0.05	0.5±0.05		
470 nF			0.5±0.05	0.5±0.05	0.5±0.05		
Ι.0 μF			0.5±0.05	0.5±0.05			
2.2 µF							
4.7 µF							
IO μF							
22 µF							
47 µF							

Table 3Sizes from 0603 to 0805

CAP.	0603					0805				
	6.3 V	10 V	16 V	25 V	50 V	6.3 V	10 V	16 V	25 V	50 V
10 nF				0.8±0.1	0.8±0.1				0.6±0.1	0.6±0.1
22 nF				0.8±0.1	0.8±0.1				0.6±0.1	0.6±0.1
47 nF				0.8±0.1	0.8±0.1				0.6±0.1	0.6±0.1
100 nF			0.8±0.1	0.8±0.1	0.8±0.1				0.6±0.1	0.6±0.1
220 nF			0.8±0.1	0.8±0.1	0.8±0.1			0.6±0.1	0.85±0.1	0.85±0.1
470 nF			0.8±0.1	0.8±0.1				0.85±0.1	0.85±0.1	0.85±0.1
Ι.0 μF	0.8±0.1	0.8±0.1	0.8±0.1	0.8±0.1				0.85±0.1	0.85±0.1	1.25±0.2
2.2 µF	0.8±0.1	0.8±0.1	0.8±0.1			0.85±0.1	0.85±0.1	0.85±0.1	1.25±0.2	
4.7 µF	0.8±0.1	0.8±0.1				0.85±0.1	0.85±0.1	1.25±0.2		
ΙΟ μF						1.25±0.2	1.25±0.2			
22 µF						1.25±0.2	1.25±0.2			
47 µF										

NOTE

I. Values in shaded cells indicate thickness class in mm

2. Capacitance value of non E-3 series is on request

Surface-Mount Ceramic Multilayer Capacitors V5V SERIES 6.3 V to 50 V

CAPACITANCE RANGE & THICKNESS FOR Y5V

Table 4 Sizes from 1206 to 1210

CAP.	1206					1210				
	6.3 V	10 V	16 V	25 V	50 V	6.3 V	10 V	16 V	25 V	50V
10 nF				0.6±0.1	0.6±0.1					
22 nF				0.6±0.1	0.6±0.1					
47 nF				0.6±0.1	0.6±0.1					
100 nF				0.6±0.1	0.6±0.1					
220 nF				0.6±0.1	0.6±0.1					
470 nF				0.85±0.1	0.85±0.1					
Ι.0 μF			0.85±0.1	0.85±0.1	0.85±0.1					
2.2 µF		0.85±0.1	0.85±0.1	0.85±0.1						
4.7 µF		0.85±0.1	0.85±0.1							
I0 μF	0.85±0.1	0.85±0.1	1.15±0.1	1.6±0.2		1.5±0.1	1.5±0.1	1.5±0.1	1.5±0.1	1.5±0.1
22 µF	1.6±0.2	1.6±0.2	1.6±0.2			1.6±0.2	1.6±0.2	1.6±0.2		
47 µF										

NOTE

I. Values in shaded cells indicate thickness class in mm

2. Capacitance value of non E-3 series is on request

THICKNESS CLASSES AND PACKING QUANTITY

Table 5							
SIZE	THICKNESS		Ø180 MM Paper	/ 7 INCH Blister	Ø330 MM / Paper	13 INCH Blister	
CODE	CLASSIFICATION	QUANTITY PER REEL		Diister		Diister	PER BULK CASE
0201	0.3 ±0.03 mm	8 mm	15,000		50,000		
0402	0.5 ±0.05 mm	8 mm	10,000		50,000		50,000
0603	0.8 ±0.1 mm	8 mm	4,000		15,000		15,000
	0.6 ±0.1 mm	8 mm	4,000		20,000		10,000
0805	0.85 ±0.1 mm	8 mm	4,000		15,000		8,000
	1.25 ±0.2 mm	8 mm		3,000		10,000	5,000
	0.6 ±0.1 mm	8 mm	4,000		20,000		
-	0.85 ±0.1 mm	8 mm	4,000		15,000		
1004	1.00 / 1.15 ±0.1 mm	8 mm		3,000		10,000	
1206	1.25 ±0.2 mm	8 mm		3,000		10,000	
-	1.6 ±0.15 mm	8 mm		2,500		10,000	
-	1.6 ±0.2 mm	8 mm		2,000		10,000	
	0.6 / 0.7 ±0.1 mm	8 mm		4,000		15,000	
	0.85 ±0.1 mm	8 mm		4,000		10,000	
	1.15 ±0.1 mm	8 mm		3,000		10,000	
	1.15 ±0.15 mm	8 mm		3,000		10,000	
	1.25 ±0.2 mm	8 mm		3,000			
1210	1.5 ±0.1 mm	8 mm		2,000			
-	1.6 / 1.9 ±0.2 mm	8 mm		2,000			
	2.0 ±0.2 mm	8 mm		2,000 1,000			
	2.5 ±0.2 mm	8 mm		l ,000 500			

Surface-Mount Ceramic Multilayer Capacitors Y5V SERIES 6.3 V to 50 V

ELECTRICAL CHARACTERISTICS

Y5V DIELECTRIC CAPACITORS; NISN TERMINATIONS

Unless otherwise specified, all test and measurements shall be made under standard atmospheric conditions for testing as given in 5.3 of IEC 60068-1:


- Temperature: 15 °C to 35 °C
- Relative humidity: 25% to 75%
- Air pressure: 86 kPa to 106 kPa


Before the measurements are made, the capacitor shall be stored at the measuring temperature for a time sufficient to allow the entire capacitor to reach this temperature.

The period as prescribed for recovery at the end of a test is normally sufficient for this purpose.

DESCRIPTION				VALUE
Capacitance range				I0 nF to 22 μF
Capacitance tolerance				±20% –20% to +80%
Dissipation factor (D.F.)	≤ 6.3 V			≤ 5%
		Exception:	0805 ≥ 22 µF	≤ 20%
	10 V			≤ 12.5%
		Exception:	$0402 \geq 680 \text{ nF}; \ \ 0603 \geq 2.2 \ \mu\text{F}; \ \ 0805 = 10 \ \mu\text{F};$	≤ 5%
			$0805 \ge 22 \ \mu F;$ $1206 \ge 10 \ \mu F$	≤ 20%
	16 V			≤ 12.5%
		Exception:	0603 ≥ 4.7 μF	≤ 15%
			I206 ≥ I0 µF	≤ 20%
	≥ 25 V			≤ 9%
		Exception:	0201 ≥ 10 nF	≤ 12.5%
Insulation resistance after	I minute at U	. (DC)	$\label{eq:Rins} Rins \geqslant 10~G\Omega~or~Rins~x~Cr \geqslant 50\\ Rins~x~Cr \geqslant 100~\Omega.F:0603~,~4.7uF,~6.3V~anc\\ Rins~x~Cr \geqslant 50\\ Rins~x~Cr \geqslant 50\\ Rins~x~Cr \gg 50$ Rins~x~Cr \gg 50\\ Rins~x~Cr \gg 50	
Maximum capacitance cha	ange as a function	on of tempe	rature	
(temperature characterist	cic/coefficient):			+22% to -82%
Operating temperature ra	ange:			–30 °C to +85 °C

Surface-Mount Ceramic Multilayer Capacitors V5V SERIES 6.3 V to 50 V





SOLDERING RECOMMENDATION

Table 7						
SOLDERING	SIZE					
METHOD	0201	0402	0603	0805	1206	≥ 1210
Reflow	Reflow only	> 100 nF	> 1.0 µF	> 2.2 µF	> 2.2 µF	Reflow only
Reflow/Wave		≤ 100 nF	≤ 1.0 µF	≤ 2.2 µF	≤ 2.2 µF	

YNM0020

50 V

50

40 50 V_{DC} (V)

Surface-Mount Ceramic Multilayer Capacitors V5V SERIES 6.3 V to 50 V

 $\frac{9}{14}$

TESTS AND REQUIREMENTS

TEST	TEST MET	HOD	PROCEDURE	REQUIREMENTS
Mounting	IEC 60384- 21/22	4.3	The capacitors may be mounted on printed-circuit boards or ceramic substrates	No visible damage
Visual inspection and dimension check		4.4	Any applicable method using × 10 magnification	In accordance with specification
Capacitance ⁽¹⁾		4.5.1	Class 2: At 20 °C, 24 hrs after annealing $f = 1 \text{ KHz}$ for $C \le 10 \mu$ F, rated voltage > 6.3 V, measuring at voltage 1 V _{rms} at 20 °C $f = 1 \text{ KHz}$, for $C \le 10 \mu$ F, rated voltage ≤ 6.3 V, measuring at voltage 0.5 V _{rms} at 20 °C $f = 120 \text{ Hz}$ for $C > 10 \mu$ F, measuring at voltage 0.5 V _{rms} at 20 °C	Within specified tolerance
Dissipation factor (D.F.) ⁽¹⁾		4.5.2	Class 2: At 20 °C, 24 hrs after annealing $f = 1 \text{ KHz}$ for $C \le 10 \mu$ F, rated voltage > 6.3 V, measuring at voltage 1 V _{rms} at 20 °C $f = 1 \text{ KHz}$, for $C \le 10 \mu$ F, rated voltage ≤ 6.3 V, measuring at voltage 0.5 V _{rms} at 20 °C $f = 120 \text{ Hz}$ for $C > 10 \mu$ F, measuring at voltage 0.5 V _{rms} at 20 °C	In accordance with specification
Insulation resistance		4.5.3	At U_r (DC) for 1 minute	In accordance with specification
Temperature characteristic		4.6	Class 2: Between minimum and maximum temperature Y5V: -30 °C to +85 °C Normal Temperature: 20 °C	<general purpose="" series=""> ΔC/C Class 2: Y5V: 22% to -82% <high capacitance="" series=""> ΔC/C Class 2: Y5V: 22% to -82%</high></general>
Adhesion		4.7	A force applied for 10 seconds to the line joining the terminations and in a plane parallel to the substrate	Force size ≥ 0603: 5N size = 0402: 2.5N size = 0201: 1N

NOTE:

I. For individual product specification, please contact local sales.

TEST	TEST METHOD		PROCEDURE	REQUIREMENTS		
Bending strength	IEC 60384- 21/22	4.8	Mounting in accordance with IEC 60384-22 paragraph 4.3	No visible damage		
			Conditions: bending 1 mm at a rate of 1 mm/s, radius jig 5 mm	<general purpose="" series=""> ΔC/C</general>		
				Class2:		
				Y5V: ±10%		
				<high capacitance="" series=""></high>		
				$\Delta C/C$		
				Class2:		
				Y5V: ±10%		
Resistance to soldering heat		4.9	Precondition: $150 + 0/-10$ °C for 1 hour, then keep for 24 ±1 hours at room temperature	Dissolution of the end face plating shall not exceed 25% of the length of the edge		
0			Preheating: for size \leq 1206: 120 °C to 150 °C for 1 minute	concerned		
			Preheating: for size >1206: 100 °C to 120 °C for 1 minute and 170 °C to 200 °C for 1 minute	<general purpose="" series=""> ΔC/C</general>		
			Solder bath temperature: 260 \pm 5 °C	Class2:		
			Dipping time: 10 ±0.5 seconds	Y5V: ±20%		
			Recovery time: 24 \pm 2 hours	<high capacitance="" series=""></high>		
				$\Delta C/C$		
				Class2:		
				Y5V: ±20%		
			-	D.F. within initial specified value		
				R_{ins} within initial specified value		
Solderability		4.10	Preheated the temperature of 80 °C to 140 °C and maintained for 30 seconds to 60 seconds.	The solder should cover over 95% of the critical area of each termination		
			I. Temperature: 235±5°C / Dipping time: 2 ±0.5 s			
			 Temperature: 23515 C / Dipping time: 2 ±0.5 s (lead free) 			
			Depth of immersion: 10mm			

Product specification $\frac{10}{14}$

Product specification 1		
	Product specification	1

۱	I	1	
	1	4	

TEST	TEST METH	OD	PROCEDURE	REQUIREMENTS
Rapid change of temperature	IEC 60384- 21/22	4.11	Preconditioning; 150 +0/-10 °C for 1 hour, then keep for 24 ±1 hours at room temperature 5 cycles with following detail: 30 minutes at lower category temperature 30 minutes at upper category temperature Recovery time 24 ±2 hours	No visual damage <general purpose="" series=""> ΔC/C Class2: Y5V: ±20% <high capacitance="" series=""> ΔC/C Class2: Y5V: ±20% D.F. meet initial specified value R_{ins} meet initial specified value</high></general>
Damp heat with U _r load		4.13	 Preconditioning, class 2 only: 150 +0/-10 °C /1 hour, then keep for 24 ±1 hour at room temp Initial measure: Spec: refer initial spec C, D, IR Damp heat test: 500 ±12 hours at 40 ±2 °C; 90 to 95% R.H. 1.0 Ur applied Recovery: Class 2: 24 ±2 hours Final measure: C, D, IR P.S. If the capacitance value is less than the minimum value permitted, then after the other measurements have been made the capacitor shall be precondition according to "IEC 60384 4.1" and then the requirement shall be met. 	No visual damage after recovery <general purpose="" series=""></general> $\Delta C/C$ Class2: $Y5V: \pm 30\%$ D.F. Class2: $Y5V: \le 15\%$ R _{ins} Class2: $Y5V: \ge 500 \text{ M}\Omega \text{ or } \text{R}_{ins} \times C_r \ge 25\text{ s}$ whichever is less <high capacitance="" series=""></high> $\Delta C/C$ Class2: $Y5V: \pm 30\%$ D.F. Class2: $Y5V: \pm 30\%$ D.F. Class2: $Y5V: \pm 30\%$ D.F. Class2: $Y5V: 2 \times \text{ initial value max}$ R_{ins} Class2: $Y5V: 2 \times \text{ initial value max}$ R_{ins} Class2: $Y5V: 500 \text{ M}\Omega \text{ or } \text{R}_{ins} \times C_r \ge 5\text{ s}$ whichever is less

14

TEST	TEST METH	HOD	PROCEDURE	REQUIREMENTS
Endurance	IEC 60384- 21/22	4.14	 I. Preconditioning, class 2 only: 150 +0/-10 °C /1 hour, then keep for 24 ±1 hour at room temp Initial measure: Spec: refer initial spec C, D, IR Endurance test: Temperature: Y5V: 85 °C Specified stress voltage applied for 1,000 hours: Applied 2.0 × U_r for general product. Applied 1.5 × U_r for high cap. product. Recovery time: 24 ±2 hours Final measure: C, D, IR P.S. If the capacitance value is less than the minimum value permitted, then after the other measurements have been made the capacitor shall be precondition according to "IEC 60384 4.1" and then the requirement shall be met. 	REQUIREMENTSNo visual damage <general purpose="" series=""> $\Delta C/C$Class2: $Y5V: \pm 30\%$D.F.Class2: $Y5V: \le 15\%$RinsClass2: $Y5V: \le 15\%$RinsClass2: $Y5V: \ge 1,000 M\Omega$ or $R_{ins} \times C_r \ge 50s$ whichever is less<high capacitance="" series=""> $\Delta C/C$Class 2: $Y5V: \pm 30\%$D.F.Class 2: $Y5V: \pm 30\%$D.F.Class 2: $Y5V: 2 \times initial value max$$R_{ins}$Class 2: $Y5V: 1,000 M\Omega$ or $R_{ins} \times C_r \ge 10s$ whichever is less</high></general>
Voltage proof	IEC 60384-1	4.6	Specified stress voltage applied for 1~5 seconds Ur ≤100 V: series applied 2.5 Ur Charge/Discharge current is less than 50 mA	No breakdown or flashover

REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 14	Dec. 21, 2023	-	- Update 0805, 10 μF, 10V D.F. value
Version 13	Aug. 10, 2023	-	- 1206, 1uF, 16V and 50V
Version 12	Dec. 14, 2022	-	- Add 0603, 220nF, 50V
Version 11	Oct. 05, 2021	-	- Update 0805, 1210 I.R. spec, modify 0402 L4 spec
Version 10	Apr. 29, 2021	-	- Update 1206 ≥ 10 μF, 16V Df value
Version 9	Nov. 11, 2019	-	- Add 0603, 4.7uF, 10V
Version 8	Mar. 7, 2017	-	- 0805 L4 spec updated
Version 7	Dec. 9, 2016	-	- Soldering recommendation update
Version 6	Jan. 12, 2016	-	- Update capacitance range & thickness
Version 5	Jul. 29, 2010	-	- Modify the last 2-digit of 12NC
Version 4	Jun. 24, 2010	-	- Dimension on 1206 case size updated
Version 3	Apr. 22, 2010	-	- Dimension updated
Version 2	Feb. 04, 2010	-	- The statement of "Halogen Free" on the cover added
Version I	Nov. 04, 2009	-	- Ordering code updated - Dimension updated
Version 0	Apr. 15, 2009	-	 New datasheet for general purpose and high capacitance Y5V series with RoHS compliant Replace the "6.3V to 50V" part of pdf files: Y5V_6.3V_10V_9_Preliminary, Y5V_10V-to-50V_10_Preliminary, Y5V_16V_25V_50V_11 Combine 0201 from pdf files: UP-NP0X5RX7RY5V_0201_6.3-to-50V_2 and UY-NPOX5RX7RY5V_0201_6.3-to-50V_2 Define global part number Description of "Halogen Free compliant" added Test method and procedure updated

<u>LEGAL DISCLAIMER</u>

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.