

Drawer cabinet system 550 S with 5 drawers

Depth 550 mm, width 722 mm


Execution:

- Solidly welded steel sheet construction
- Tilt-proof due to built-in individual drawer pull-out locking
- The drawers have high-quality Delrin rollers which means that they run quietly
- Drawers with slots all around for inserting compartment rails and dividers
- Perforated steel sheet base (25 mm hole spacing) for fastening and fixing components
- Aluminium grip handles with paper and cellophane strips and lateral cover caps

Advantage:

- Optimum operating characteristics of drawers
- High quality - made in Germany

Art. no.	50295 012
Brand	HK
Manufacturer Part Number	50295012
Number of drawers	5 PCS
With doors	No
Height	1036 mm
Width	722 mm
Depth	550 mm
Height x width x depth	1036 x 722 x 550 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	600 x 450 mm
Drawer with slots	Yes
Perforated drawer base	Yes
Load-carrying capacity per drawer	100 kg
Drawer surface	0.27 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	No
With single pull-out safety brake	Yes
Central locking	Yes
Material of cover panel	Wood, plastic-coated
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Functions	RFID possible
Model	S5 32/5
Overall surface	1.35 m ²
Lock type	DOM® locking system
Material	Sheet steel
Gross Weight	105.000 kg
Product Group	5BB



EAN

4039247461875